

VS-ST-CD-1,0/14,8/0,5-R - Crimp contact



1689556

<https://www.phoenixcontact.com/us/products/1689556>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, for D-SUB contact inserts with standard contact density, pin, connection cross section AWG 24 ... 20, punched, gold-plated

Similar figure

Commercial data

Item number	1689556
Packing unit	10,000 pc
Minimum order quantity	10,000 pc
Note	Made to order (non-returnable)
Sales key	AB19
Product key	ABNCAC
GTIN	4017918895266
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	0.076 g
Customs tariff number	85366990
Country of origin	DE

VS-ST-CD-1,0/14,8/0,5-R - Crimp contact



1689556

<https://www.phoenixcontact.com/us/products/1689556>

Technical data

Notes

Order information:	Type of packaging: roll, unrolls from left
--------------------	--

Mounting

Mounting type	Crimp connection
---------------	------------------

Product properties

Product type	Crimp contact
Contact material type	rolled

Connection data

Connection technology

Contact connection type	Pin
Connection method	Crimp connection

Conductor connection

Stripping length	2.4 mm
Connection cross section (flexible)	0.2 mm ² ... 0.5 mm ²
Connection cross section (rigid)	0.2 mm ² ... 0.5 mm ²
Connection cross section AWG (rigid)	24 ... 20
Connection cross section AWG (flexible)	24 ... 20

Material specifications

Material Contact	Metal
------------------	-------

Dimensions

Diameter (Contact diameter)	1 mm
-----------------------------	------

Electrical properties

Rated current (Maximum load current)	7.5 A
--------------------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

VS-ST-CD-1,0/14,8/0,5-R - Crimp contact



1689556

<https://www.phoenixcontact.com/us/products/1689556>

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

ETIM

ETIM 10.0	EC002943
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

VS-ST-CD-1,0/14,8/0,5-R - Crimp contact



1689556

<https://www.phoenixcontact.com/us/products/1689556>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com