

# VS-25-BU-DSUB-CD-B - D-SUB contact support



1689967

<https://www.phoenixcontact.com/us/products/1689967>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 3, for 25 signal contacts, type of contact socket, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-25-..



## Your advantages

- D-SUB 25 connection
- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

## Commercial data

Item number	1689967
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918914363
Weight per piece (including packing)	11.89 g
Weight per piece (excluding packing)	9.33 g
Customs tariff number	85366990
Country of origin	DE

# VS-25-BU-DSUB-CD-B - D-SUB contact support



1689967

<https://www.phoenixcontact.com/us/products/1689967>

## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	25
Connection profile	D-SUB
Number of slots	1
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	18.1 mm
Height	12.93 mm
Length	53.42 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

### Environmental and real-life conditions

# VS-25-BU-DSUB-CD-B - D-SUB contact support



1689967

<https://www.phoenixcontact.com/us/products/1689967>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 130 °C

## Mounting

Mounting type	Screw mounting
---------------	----------------

# VS-25-BU-DSUB-CD-B - D-SUB contact support



1689967

<https://www.phoenixcontact.com/us/products/1689967>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1689967>



**UL Recognized**

Approval ID: E118976

1689967

<https://www.phoenixcontact.com/us/products/1689967>

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 10.0	EC001132
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-25-BU-DSUB-CD-B - D-SUB contact support



1689967

<https://www.phoenixcontact.com/us/products/1689967>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)