

HC-B 24-TMS-100/O1M40G-EMV - EMC housing



1691052

<https://www.phoenixcontact.com/us/products/1691052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON ADVANCE EMC sleeve housing B24, with screw locking, height 100 mm, with 1xM40 support, and straight cable outlet

Commercial data

Item number	1691052
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7AAA
GTIN	4017918616526
Weight per piece (including packing)	511.24 g
Weight per piece (excluding packing)	511.24 g
Country of origin	DE

1691052

<https://www.phoenixcontact.com/us/products/1691052>

Technical data

Product properties

Product type	Housing with screw locking
Housing type	Sleeve housing
Application	EMC
Type	B24
Type of the screw connection	1x M40
Fixing screws	M6
Cable outlet	straight

Connection data

Tightening torque	3 Nm (Locking screw)
-------------------	----------------------

Dimensions

Width	57 mm
Height	100 mm
Length	152 mm

Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	112 mm

Material specifications

Seal material	NBR, conductive
Housing material	Die-cast aluminum
Housing surface material	EMC coating, silver
Locking latch material	Stainless steel

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (0.2 bar/24 h)
	IP69K
Enclosure rating (NEMA)	4 (NEMA 250)
	4X (NEMA 250)
	6P (NEMA 250)
	NEMA 250
Ambient temperature (operation)	-40 °C ... 125 °C

Mechanical properties

Mechanical data

Type of the screw connection	1x M40
------------------------------	--------

1691052


<https://www.phoenixcontact.com/us/products/1691052>

Mounting

Assembly note	In order to guarantee that the protective conductor contact functions even when plugged in at an angle, the two panel-mount flanges must have sufficient electrical contact with the metal mounting panel. To ensure optimum shielding, any insulating power coating must be removed from the profile gasket area on the control cabinet panel. Tightening torque of locking screw: 3 Nm.
Fixing screws	M6

Drawings

Drilling plan/solder pad geometry



Mounting cutout

a = when self-tapping M4 Torx® screws with a diameter of 3.6 mm are used, or when M4 screws with M4 thread or 4.5 mm diameter are used

HC-B 24-TMS-100/O1M40G-EMV - EMC housing



1691052

<https://www.phoenixcontact.com/us/products/1691052>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

HC-B 24-TMS-100/O1M40G-EMV - EMC housing



1691052

<https://www.phoenixcontact.com/us/products/1691052>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com