PSD-SL AE-P - Acoustic signaling device

1691145

https://www.phoenixcontact.com/us/products/1691145

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Buzzer, 15 acoustic signals, 24 V DC, point design

Product description

The buzzer is intended for signaling functional states in machines and systems. Up to 15 different tones enable differentiated signaling. The buzzer features a UV-resistant housing with a 5-pos. M12 device connection and an M22 thread for mounting. The device is connected via a 5-pos. M12 connector and can be controlled with positive or negative switching.

Your advantages

- Function-oriented signaling
- Numerous acoustic signals
- Quick and easy mounting and installation
- Rugged design

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1691145
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL112
GTIN	4067923252486
Weight per piece (including packing)	64 g
Weight per piece (excluding packing)	0.05 g

Customs tariff number	85318070
Country of origin	AT

Technical data

Product properties

Product type	Signaling device
Product family	PSD-SL

Electrical properties

Power consumption	max. 0.8 W

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	10 V DC ... 30 V DC
Pulse current	max. 81 mA
Leakage current	1 mA
Inrush current	0.5 A

Output data

Leakage current	1 mA

Connection data

Connection method	M12 connector, 5-pos.

Signaling

Signal element type	acoustic
Type of acoustic signal	Continuous tone
	Pulse tone
	Alternating tone
	Beep
	Sweep tone
	Sinusoidal tone
	Emergency beep (DIN emergency beep, Germany)
Number of tones	15
Volume	max. 90 db(A)

Dimensions

Item dimensions

Height	55 mm
Diameter	50 mm

Calotte

Height	24 mm

Material specifications

Color (Housing)	black (RAL 9005)

Material	Polycarbonate (UV stabilized)

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 0.4 g ... 12 g, 10 Hz ... 55 Hz, amplitude 1.0 mm, sweep 5 min., dwell time 30 min.
Vibration resistance in accordance with MIL-STD-202F	: 10g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms period, half-sine shock pulse

Environmental and real-life conditions

Ambient conditions


Degree of protection (IP)	IP66
	IP67
	IP69
	IP6K9K (In accordance with ISO 20653)
Degree of protection (UL type)	UL Type 4
	UL Type 4X
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Single-hole mounting (M22 thread)
Mounting position	any

Drawings

Dimensional drawing



Dimensions (in mm)

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1691145

cULus Listed
Approval ID: E140324

Classifications

ECLASS

ECLASS-13.0	27371220
ECLASS-15.0	27371220

ETIM

ETIM 10.0	EC000232

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com