


ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled PCB connector / Y-cable with 2 printed circuit board connectors, rated current: 9 A, Head 1: 3-position , pitch: 5.08 mm , Crimp connection , Pin, Cable 1: cable length: 0.33 m, Color: black, blue, Cable type:mPPE litz wire, Head 2: 3-position, pitch: 5 mm , Push-in spring connection , Socket, Cable 2: cable length: 0.2 m, Color: black, blue, Cable type:mPPE litz wire, product feature: PCB connectors for Smart Meter Gateways (SMGW), product range: CC-Cabeling SMGW

Product description

PCB connectors for Smart Meter Gateways (SMGW)

Your advantages

- Male connector with straight or bent conductor exit for optimal installation in control cabinets
- Handling-compatible cable lengths, harmonized with meter design 3.HZ
- Connection technology compatible with all FNN-compliant base meters, gateways, and control boxes
- Simple connection of auxiliary equipment using Y-cables with open conductor ends

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1714316 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Product key | AAHRDB |
| GTIN | 4055626356839 |
| Weight per piece (including packing) | 19.63 g |
| Weight per piece (excluding packing) | 20.264 g |
| Country of origin | DE |

ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

Technical data

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | Assembled PCB connector |
| Product family | CC-Cabeling SMGW |
| Product line | COMBICON Connectors Special |
| Number of positions | 1 |
| Pitch | 0.00 mm |
| Number of connections | 2 |
| Number of potentials | 2 |

Electrical properties

Properties

| | |
|-----------------------|-----|
| Nominal current I_N | 9 A |
|-----------------------|-----|

Notes

| | |
|--------------------|--|
| Notes on operation | PCB connectors without switching power in accordance with IEC 61984 for Smart Meter Gateways (SMGW). When used for their intended purpose, they must not be plugged in or disconnected live or under load. |
|--------------------|--|

Mechanical tests

Tensile strength of crimp connections

| | |
|---|----------------------|
| Result | Test passed |
| Conductor cross-section/conductor type/tractive force setpoint/actual value | AWG 18 / ≥ 85 N |

Insertion and withdrawal forces

| | |
|-------------------------------------|-------------|
| Result | Test passed |
| Insertion strength per pos. approx. | 10 N |
| Withdraw strength per pos. approx. | 10 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -30 °C ... 70 °C |
| Relative humidity (storage/transport) | 30 % ... 70 % |
| Ambient temperature (assembly) | -5 °C ... 100 °C |

Ambient conditions

| | |
|---|---|
| Ambient temperature (storage/transport) | -30 °C ... 70 °C |
| Relative humidity (storage/transport) | 30 % ... 70 % |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Ambient temperature (installation) | -40 °C ... 100 °C (dependent on the derating curve) |

ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

| | |
|---|--|
| Ambient temperature (mobile installation) | -5 °C ... 100 °C (dependent on the derating curve) |
|---|--|

Connector

Connection 1

| | |
|----------------------------|---------------------|
| Range of articles | ICC 2,5/...-STZ |
| Pitch | 5.08 mm |
| Connection method | Crimp connection |
| Number of positions | 3 |
| Nominal cross section | 2.5 mm ² |
| Contact connection type | Pin |
| Mounting type | without |
| Color | green |
| Insulating material | PA |
| CTI according to IEC 60112 | 600 |

Connection 2

| | |
|-------------------------|---------------------------|
| Range of articles | TVFKC 1,5/...-ST |
| Connection method | Push-in spring connection |
| Pitch | 5 mm |
| Number of positions | 3 |
| Nominal cross section | 1.5 mm ² |
| Contact connection type | Socket |
| Mounting type | without |
| Color | green |

Cable/line

| | |
|---------------------------------|---|
| Cable length | 0.33 m |
| UL AWM Style | 11028 |
| Shielded | no |
| Conductor structure signal line | 19x 0.25 mm |
| AWG signal line | 18 |
| Conductor cross-section | 2x 0.82 mm ² |
| Wire diameter incl. insulation | 1.85 mm |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | mPPE |
| Single wire, color | black, blue |
| Thickness, insulation | 0.29 mm |
| Max. conductor resistance | ≤ 19 Ω/m |
| Insulation resistance | ≥ 20 MΩ*km |
| Nominal voltage, cable | 600 V |
| Test voltage | 6000 V |
| Ambient temperature (operation) | -40 °C ... 105 °C (cable, fixed installation) |
| UL AWM Style | 11028 |

ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

| | |
|---------------------------------|---|
| Shielded | no |
| Conductor structure signal line | 19x 0.25 mm |
| AWG signal line | 18 |
| Conductor cross-section | 2x 0.82 mm ² |
| Wire diameter incl. insulation | 1.85 mm |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | mPPE |
| Single wire, color | black, blue |
| Thickness, insulation | 0.29 mm |
| Max. conductor resistance | ≤ 19 Ω/m |
| Insulation resistance | ≥ 20 MΩ*km |
| Nominal voltage, cable | 600 V |
| Test voltage | 6000 V |
| Ambient temperature (operation) | -40 °C ... 105 °C (cable, fixed installation) |

Packaging specifications

| | |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

Drawings



Type: ICC/TVFKC/AI8/3P13L33-20SMGW

ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27469090 |
| ECLASS-15.0 | 27469090 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

ICC/TVFKC/AI8/3P13L33-20SMGW - Assembled PCB connectors



1714316

<https://www.phoenixcontact.com/us/products/1714316>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | 4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated(CAS: n/a) |
| SCIP | 56fb22d2-6f11-4607-9aeb-853ad942d443 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.668 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com