

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



12-Port Ethernet-APL Field switch, Zone 2 mountable, Ex 'ic' APL ports, four uplink ports, Power Class A ports

Your advantages

- Redundant power connections
- APL-managed switch
- Top-down wiring terminations
- PROFINET-managed switch
- Connects to Ex ic devices in Zone 2 hazardous locations using 2-WISE, FISCO, or intrinsically safe entity parameters
- Global approvals
- MRP and S2 PROFINET System Redundancy

Commercial data

Item number	1718554
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN99
Product key	DNN128
GTIN	4067923269330
Weight per piece (including packing)	2,473 g
Weight per piece (excluding packing)	2,177.4 g
Customs tariff number	85176200
Country of origin	US

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch




1718554

<https://www.phoenixcontact.com/us/products/1718554>

Technical data

Dimensions

Dimensional drawing	
	
Width	150 mm
Height	215 mm
Depth	127 mm
Note on dimensions	Depth when installed on a NS 35/15 DIN rail

Notes

Note on application	
Note on application	Only for industrial use
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area

Material specifications

Color (Housing)	gray (RAL 7042)
Color (Cover)	light gray (RAL 7035)
Housing material	Die-cast aluminum
	PC

Mounting

Mounting type	DIN rail mounting
	Panel mount
Useable DIN rail type	NS 35/15
	NS 35/15

Interfaces

Ethernet (RJ45)	
Number of interfaces	2
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	2 (RJ45 ports)

Ethernet (SFP)

Number of interfaces	2
Connection method	SFP
Note on the connection method	Full duplex
Transmission speed	100/1000 Mbps (full duplex)
Transmission physics	FO
Transmission length	Depending on the SFP module used
No. of channels	2 (SFP ports)

Ethernet (APL)

Connection method	Screw connection
Note on the connection method	APL, full duplex
Transmission speed	10 Mbps
Transmission physics	Copper
No. of channels	12 (APL ports)

Power Source Equipment (PSE) Port: Class A

Power Class	SPAA
Note	Each port configurable via software
Output nominal voltage	≥ 9.6 V DC
Output current	≥ 55.56 mA
Output power	≥ 0.54 W

Product properties

Product type	Switch
Product family	Managed APL Switch
MTTF	83.26 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	42.17 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	10.29 Years (SN 29500 standard, temperature 55°C, operating cycle 100%)
Special properties	Zone 2 mountable
	Ex 'ic' APL ports
	four uplink ports

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
Overvoltage category	II
Degree of pollution	2

Switch functions

RMON History

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Diagnostic functions	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
	N:1-Portmirroring
	ACD (Address Conflict Detection)
	SysLog
	CRC-Surveillance
Filter functions	Quality of Service (8 priority classes)
	Class of Service
	DiffServ/DSCP
	Port prioritization
	VLAN (up to 32 VLANs)
	IGMP Snooping/Querier (v1/v2)
	Auto-Query-Port
	Extended Multicast Filtering
IP parameterization	DHCP client
	DHCP Option 82 (Relay Agent)
	DHCP server (pool-based, port-based)
	BootP
	DCP (Discovery and Configuration Protocol)
MAC address table	8k
Management	Web-based management (HTTP/HTTPS)
	Role-based user management (LDAP, RADIUS)
	SNMPv1/v2/v3
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	Large Tree Support
	LACP (Link Aggregation Control Protocol)
	PROFINET S2 system redundancy
Time synchronization	SNTP (Simple Network Time Protocol)

Electrical properties

Power consumption	8 W (No-load)
	max. 20.9 W (12 Class A ports at max. load (22 V DC supply voltage at 70°C))
Maximum power dissipation for nominal condition	14 W (12 Class A ports at max. load (22 V DC supply voltage at 70°C))
Test section	Supply Voltage/spurs 1500 V ACrms
	100BASE-T / Spurs 1500 V ACrms
	SFP / Spurs 1500 V ACrms
	Spurs / Earth Ground (Housing) 500 V ACrms
	Block of Spurs / Block of Spurs 500 V ACrms
	Supply / 100BASE-T 2000 V ACrms
	100BASE-T / 100BASE-T 2000 V ACrms
	Supply / SFP 1500 V ACrms

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	22 V DC ... 30 V DC (redundant)
Max. current consumption	1 A

Connection data

Power supply

Connection method	Screw connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (maximum)
Permissible humidity (operation)	0 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	15g (IEC 60068-2-27)
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

ATEX

Identification	⊕ II 3(3)G Ex ic ec [ic] IIC T4 Gc
	II (3) D [Ex ic Dc] IIIC
Certificate	U 25 ATEX 3482X

IECEx

Identification	Ex ic ec [ic] IIC T4 Gc
	[Ex ic Dc] IIIC
Certificate	IECEx UL 25.0071X

UL, USA/Canada

Identification	Ind. Cont. Eq. E238705 also Listed
	Ind. Cont. Eq. for haz. loc. E196811
	Install in: Class I, Div. 2, Groups A, B, C, D T4
	Nonincendive field wiring outputs for: Class I, Div. 2, Groups A, B, C, D; Class II, Div. 2, Groups F, G; Class III, Div. 2 haz. loc.
	Class I, Zone 2, AEx ic ec [ic] IIC T4 Gc, [AEx ic Dc] IIIB

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

	Ex ic ec [ic] IIC T4 Gc X
	[Ex ic Dc] IIIC X
CCC Ex	
Identification	Ex ic ec [ic] IIC T4 Gc
	[Ex ic Dc] IIIC
INMETRO	
Identification	Ex ic ec [ic] IIC T4 Gc
	[Ex ic Dc] IIIC
Certificate	DNV 26.0115 X

Ex data

Safety data

Max. output voltage U_o	13.23 V
Max. output current I_o	341.6 mA
Max. output power P_o	1.23 W
Safety-related maximum voltage U_m	60 V
IIC: Max. external inductivity L_o / Max. external capacitance C_o	0.14 mH / 0.5 μ F
IIB/IIIB: Max. external inductivity L_o / Max. external capacitance C_o	1.2 mH / 1.5 μ F
IIA: Max. external inductivity L_o / Max. external capacitance C_o	2.39 mH / 1.8 μ F

Safety data

IIC: Max. external inductivity L_o / Max. external capacitance C_o	0.14 mH / 0.5 μ F
IIB, IIIC/IIIB: Max. external inductivity L_o / Max. external capacitance C_o	1.2 mH / 1.5 μ F
IIA: Max. external inductivity L_o / Max. external capacitance C_o	2.39 mH / 1.8 μ F

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU (Test requirements for NE 21, IEC 61326-7 also considered as per the APL EMC specifications)
Conformance with EMC directives	EN 61000-6-2 EN 61000-4-2 (ESD) Criterion A, ± 6 kV contact discharge, ± 8 kV air discharge
	EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A, Field intensity: 10 V/m
	EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A, supply lines: ± 2 kV, signal/data lines: ± 1 kV
	EN 61000-6-2 EN 61000-4-5 (surge) Criterion A, ± 1 kV supply line L-PE; ± 1 kV supply line N-PE; ± 1 kV shielded I/O signal lines for metallic enclosure devices
	EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A, 10 Vrms
	EN 61000-6-2 IEC 61000-4-16 (common mode disturbances) Criterion A: 10V (10 kHz to 150 kHz)
	EN 61000-6-4 EN 55011 (emitted interference) Class A
Noise immunity	EN 61000-6-2

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------


FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Drawings




FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch

1718554

<https://www.phoenixcontact.com/us/products/1718554>

Application drawing



FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1718554>



cULus Listed

Approval ID: E238705-20250910



IECEx

Approval ID: IECEx UL 25.0071X



cULus Listed

Approval ID: E196811-20251120

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554
<https://www.phoenixcontact.com/us/products/1718554>

Classifications

ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

ETIM

ETIM 10.0	EC000734
-----------	----------

FL SWITCH APL 2212-4A-221 - Industrial Ethernet Switch



1718554

<https://www.phoenixcontact.com/us/products/1718554>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com