


# PST 1,0/ 6-3,5 R56 - Pin strip

1720262

<https://www.phoenixcontact.com/us/products/1720262>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows an 8-pos. version of the item in tape-on-reel packing

Pin strip, nominal cross section: 0.5 mm<sup>2</sup>, color: black, nominal current: 8 A (depends on the plug used), rated voltage (III/2): 250 V, contact surface: Sn, contact connection type: Pin, number of potentials: 6, number of rows: 1, number of positions: 6, number of connections: 6, product range: PST 1,0/..-V, pitch: 3.5 mm, mounting: THR soldering / wave soldering, pin layout: Linear pinning, solder pin [P]: 3.8 mm, plug-in system: COMBICON PST 1,0, locking: without, mounting method: without, type of packaging: 56 mm wide tape, The maximum current depends on the plug used. The lower of the two current values apply for plug and pin strip. The pin strip is made of highly temperature resistant plastic and is thus suitable for the reflow process.

## Your advantages

- Suitable for wave and reflow soldering processes
- Optimum pin geometry for all COMBICON pin strip connectors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1720262       |
| Packing unit                         | 250 pc        |
| Minimum order quantity               | 250 pc        |
| Sales key                            | AA02          |
| Product key                          | AABTKA        |
| GTIN                                 | 4046356115872 |
| Weight per piece (including packing) | 3.084 g       |
| Weight per piece (excluding packing) | 2.822 g       |
| Customs tariff number                | 85366930      |
| Country of origin                    | PL            |

# PST 1,0/ 6-3,5 R56 - Pin strip



1720262

<https://www.phoenixcontact.com/us/products/1720262>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Pin strip             |
| Product family        | PST 1,0/..-V          |
| Product line          | COMBICON Connectors S |
| Type                  | Pin strip             |
| Number of positions   | 6                     |
| Pitch                 | 3.5 mm                |
| Number of connections | 6                     |
| Number of rows        | 1                     |
| Number of potentials  | 6                     |
| Mounting type         | without               |
| Pin layout            | Linear pinning        |

### Electrical properties

#### Properties

|                             |                                |
|-----------------------------|--------------------------------|
| Nominal current $I_N$       | 8 A (depends on the plug used) |
| Nominal voltage $U_N$       | 250 V                          |
| Contact resistance          | 1.8 m $\Omega$                 |
| Rated voltage (III/3)       | 160 V                          |
| Rated surge voltage (III/3) | 2.5 kV                         |
| Rated voltage (III/2)       | 250 V                          |
| Rated surge voltage (III/2) | 2.5 kV                         |
| Rated voltage (II/2)        | 250 V                          |
| Rated surge voltage (II/2)  | 2.5 kV                         |

### Mounting

|               |                                |
|---------------|--------------------------------|
| Mounting type | THR soldering / wave soldering |
| Pin layout    | Linear pinning                 |

### Material specifications

#### Material data - contact

|   |  |
|---|--|
| Note  | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy   |
| Surface characteristics                     | Tin-plated   |
| Metal surface contact area (top layer)      | Tin (3 $\mu\text{m}$ - 5 $\mu\text{m}$ Sn)                                       |
| Metal surface contact area (middle layer)   | Nickel (1 $\mu\text{m}$ - 3 $\mu\text{m}$ Ni)                                    |
| Metal surface soldering area (top layer)    | Tin (3 $\mu\text{m}$ - 5 $\mu\text{m}$ Sn)                                       |
| Metal surface soldering area (middle layer) | Nickel (1 $\mu\text{m}$ - 3 $\mu\text{m}$ Ni)                                    |

#### Material data - housing

# PST 1,0/ 6-3,5 R56 - Pin strip

1720262


<https://www.phoenixcontact.com/us/products/1720262>

|   |              |
|---|--------------|
| Color (Housing)   | black (9005) |
| Insulating material   | PA           |
| Insulating material group   | IIIa         |
| CTI according to IEC 60112  | 250          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Notes

|                     |   |
|---------------------|---|
| Note on application | Pick and place pads may protrude beyond the components. The PCB layout must ensure that collisions are avoided when components are assembled. |
|---------------------|---|

## Dimensions

|                       |  |
|-----------------------|--|
| Dimensional drawing   |  |
| Pitch                 | 3.5 mm   |
| Width [w]             | 20.6 mm  |
| Height [h]            | 13 mm  |
| Length [l]            | 2.8 mm   |
| Installed height      | 9.2 mm   |
| Solder pin length [P] | 3.8 mm   |
| Pin dimensions        | ø 1 mm   |

## PCB design

|               |         |
|---------------|---------|
| Pin spacing   | 3.50 mm |
| Hole diameter | 1.2 mm  |

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Insertion and withdrawal forces

|               |             |
|---------------|-------------|
| Result        | Test passed |
| No. of cycles | 10          |

# PST 1,0/ 6-3,5 R56 - Pin strip



1720262

<https://www.phoenixcontact.com/us/products/1720262>

|                                     |     |
|-------------------------------------|-----|
| Insertion strength per pos. approx. | 6 N |
| Withdraw strength per pos. approx.  | 5 N |

## Contact holder in insert

|  |                     |
|--|---------------------|
| Specification                                  | IEC 60512-8:1993-01 |
| Contact holder in insert<br>Requirements >20 N | Test passed         |

## Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 16                    |

### Insulation resistance

|  |                       |
|--|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | 10 <sup>12</sup> Ω    |

### Temperature cycles

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Air clearances and creepage distances |

|  |                     |
|--|---------------------|
| Specification  | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI 250             |
| Rated insulation voltage (III/3)                       | 160 V               |
| Rated surge voltage (III/3)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm              |
| minimum creepage distance (III/3)                      | 2.5 mm              |
| Rated insulation voltage (III/2)                       | 250 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |
| minimum creepage distance (III/2)                      | 2.5 mm              |
| Rated insulation voltage (II/2)                        | 250 V               |
| Rated surge voltage (II/2)                             | 2.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 1.5 mm              |
| minimum creepage distance (II/2)                       | 2.5 mm              |

## Environmental and real-life conditions

### Durability test

|  |                     |
|--|---------------------|
| Specification                          | IEC 60512-5:1992-08 |
| Impulse withstand voltage at sea level | 2.95 kV             |

# PST 1,0/ 6-3,5 R56 - Pin strip

1720262

<https://www.phoenixcontact.com/us/products/1720262>

|                             |                |
|-----------------------------|----------------|
| Contact resistance $R_1$    | 1.8 m $\Omega$ |
| Contact resistance $R_2$    | 1.9 m $\Omega$ |
| Insertion/withdrawal cycles | 10             |

## Climatic test

|                                   |   |
|-----------------------------------|---|
| Specification                     | ISO 6988:1985-02  |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h  |
| Power-frequency withstand voltage | 1.39 kV   |

## Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:1995-03       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |


## Ambient conditions

|   |   |
|---|---|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |

## Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications

|                             |  |
|-----------------------------|--|
| Dimensional drawing         |  |
| Type of packaging           | 56 mm wide tape  |
| [W] tape width              | 56 mm  |
| [W2] coil overall dimension | ≤ 62.4 mm  |
| [A] coil diameter           | ≤ 330 mm   |
| Outer packaging type        | Transparent-Bag  |

# PST 1,0/ 6-3,5 R56 - Pin strip



1720262

<https://www.phoenixcontact.com/us/products/1720262>



## Drawings

Dimensional drawing




# PST 1,0/ 6-3,5 R56 - Pin strip


1720262

<https://www.phoenixcontact.com/us/products/1720262>




Dimensional drawing





Derating curve for: PTDA 1,5/...-PH-3,5 with PST 1,0/...-3,5




Type: PT 1,5/...-PH-3,5 with PST 1,0/...-3,5

# PST 1,0/ 6-3,5 R56 - Pin strip

1720262

<https://www.phoenixcontact.com/us/products/1720262>



Type: PT 1,5/...-PVH-3,5 with PST 1,0/...-3,5

# PST 1,0/ 6-3,5 R56 - Pin strip





1720262

<https://www.phoenixcontact.com/us/products/1720262>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1720262>

|  <b>cULus Recognized</b><br>Approval ID: E60425-20030211 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B   |                       |                       |                   |                             |
|   | 300 V                 | 10 A                  | -                 | -                           |

|  <b>VDE Gutachten mit Fertigungsüberwachung</b><br>Approval ID: 40040542 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 250 V                 | 8 A                   | -                 | -                           |

# PST 1,0/ 6-3,5 R56 - Pin strip



1720262

<https://www.phoenixcontact.com/us/products/1720262>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PST 1,0/ 6-3,5 R56 - Pin strip



1720262

<https://www.phoenixcontact.com/us/products/1720262>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)