

# PV-AS-MC4/6-150-MN-SET - Photovoltaic adapter set



1704982

<https://www.phoenixcontact.com/us/products/1704982>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The SUNCLIX adapter set enables SUNCLIX connectors to be connected to type MC4 connectors from Multi Contact without voiding the product warranty or guarantee for the MC4 connectors.

## Product description

Adapter set for photovoltaic connectors for connecting SUNCLIX connectors to type MC4 connectors from Multi Contact

## Commercial data

Item number	1704982
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB02
Product key	ABLBZC
GTIN	4046356762922
Weight per piece (including packing)	83.25 g
Weight per piece (excluding packing)	83.25 g
Customs tariff number	85446010
Country of origin	DE

## Technical data

### Notes

Notes on operation	Connect these connectors only to other connectors of the same type made by the same manufacturer. When making the connections, always observe the specifications regarding nominal voltage and nominal current. The smallest common value is permissible.
--------------------	---

### Product properties

Type	Adapter
------	---------

#### Insulation characteristics

Protection class	II
------------------	----

### Electrical properties

Maximum load current	30 A (85 °C)
Rated surge voltage (III/2)	6 kV
Rated current	30 A
Contact resistance	< 1 mΩ ((incl. cable))

### Connection data

Maximum load current	30 A (85 °C)
----------------------	--------------

### Dimensions

Length	150 mm
--------	--------

### Material specifications

Color	black
Color of the housing part	black
Flammability rating according to UL 94	V0
Housing material	PPE

### Cable/line

Cable length	150 mm
Cable type	Multi-standard
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	flexible
External cable diameter	6.6 mm ... 7 mm (Bending radius: 29.6 mm)
External sheath, color	black

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP67 (1 h/1 m)
Degree of protection (not plugged in)	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (-40 °C ... 70 °C (UL))

# PV-AS-MC4/6-150-MN-SET - Photovoltaic adapter set



1704982

<https://www.phoenixcontact.com/us/products/1704982>

## Standards and regulations

Connection in acc. with standard

DIN EN 50521 (in accordance with)

1704982

<https://www.phoenixcontact.com/us/products/1704982>

## Classifications

### ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440192

### ETIM

ETIM 9.0	EC002943
----------	----------

# PV-AS-MC4/6-150-MN-SET - Photovoltaic adapter set



1704982

<https://www.phoenixcontact.com/us/products/1704982>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)