

# SPT 2,5/11-V-5,0-EX - PCB terminal block




1732580

<https://www.phoenixcontact.com/us/products/1732580>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB terminal block, nominal current: 22 A, nominal cross section: 2.5 mm<sup>2</sup>, number of potentials: 11, number of rows: 1, number of positions per row: 11, product range: SPT 2,5/..-V-EX, pitch: 5 mm, connection method: Push-in spring connection, mounting: Wave soldering, conductor/PCB connection direction: 90 °, color: green, Pin layout: Linear pinning, Solder pin [P]: 2.5 mm, number of solder pins per potential: 2, type of packaging: packed in cardboard



## Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Clamping space opened by means of fixed screwdriver enables convenient conductor connection
- Operation and conductor connection from one direction enable integration into front of device
- Satisfies the more stringent safety requirements of "Ex eb" protection according to IEC 60079-7 for potentially explosive areas
- Two solder pins reduce the mechanical strain on the soldering spots

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1732580                        |
| Packing unit                         | 50 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Product key                          | AAMBFC                         |
| GTIN                                 | 4046356282901                  |
| Weight per piece (including packing) | 14.3 g                         |
| Weight per piece (excluding packing) | 13.26 g                        |
| Country of origin                    | PL                             |

# SPT 2,5/11-V-5,0-EX - PCB terminal block



1732580

<https://www.phoenixcontact.com/us/products/1732580>

## Technical data

### Product properties

|                           |                      |
|---------------------------|----------------------|
| Product type              | PCB terminal block   |
| Product family            | SPT 2,5/...-V-EX     |
| Product line              | COMBICON Terminals M |
| Number of positions       | 11                   |
| Pitch                     | 5 mm                 |
| Number of connections     | 11                   |
| Number of rows            | 1                    |
| Number of potentials      | 11                   |
| Pin layout                | Linear pinning       |
| Solder pins per potential | 2                    |

### Electrical properties

#### Properties

|   |                          |
|---|--------------------------|
| Nominal current $I_N$                   | 22 A                     |
| Nominal voltage $U_N$                   | 176 V                    |
| Rated current / conductor cross-section | 22 A/2.5 mm <sup>2</sup> |

### Ex data

#### Ex approval

|                                 |   |
|---------------------------------|---|
| Identification                  | 0344 <sup>Ⓢ</sup> II 2GD / Ex eb IIC Gb |
| EU-type examination certificate | KEMA 07ATEX0193 U                       |
| IECEx certificate               | IECEx KEM 07.0057 U                     |

### Connection data

#### Connection technology

|                       |                     |
|-----------------------|---------------------|
| Nominal cross section | 2.5 mm <sup>2</sup> |
|-----------------------|---------------------|

#### Conductor connection

|   |  |
|---|--|
| Connection method   | Push-in spring connection  |
| Conductor cross-section rigid   | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                            |
| Conductor cross-section flexible  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                          |
| Conductor cross-section AWG   | 24 ... 14  |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Stripping length 8 mm) |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve    | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Stripping length 8 mm) |
| Stripping length  | 10 mm  |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Wave soldering |
| Pin layout    | Linear pinning |

# SPT 2,5/11-V-5,0-EX - PCB terminal block

1732580

<https://www.phoenixcontact.com/us/products/1732580>

## Material specifications


### Material data - contact

|  |  |
|--|--|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy   |
| Surface characteristics                  | hot-dip tin-plated   |
| Metal surface terminal point (top layer) | Tin (4 µm - 8 µm Sn)   |
| Metal surface soldering area (top layer) | Tin (4 µm - 8 µm Sn)   |

### Material data - housing

|   |              |
|---|--------------|
| Color (Housing)   | green (6021) |
| Insulating material   | PA           |
| Insulating material group   | I            |
| CTI according to IEC 60112  | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Dimensions

|                       |  |
|-----------------------|--|
| Dimensional drawing   |  |
| Pitch                 | 5 mm   |
| Width [w]             | 56.4 mm  |
| Height [h]            | 16.9 mm  |
| Length [l]            | 13.5 mm  |
| Installed height      | 14.4 mm  |
| Solder pin length [P] | 2.5 mm   |
| Pin dimensions        | 0.8 x 0.8 mm   |

### PCB design

|               |        |
|---------------|--------|
| Pin spacing   | 8.2 mm |
| Hole diameter | 1.2 mm |

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Relative humidity (storage/transport)   | 30 % ... 70 %    |

# SPT 2,5/11-V-5,0-EX - PCB terminal block



1732580

<https://www.phoenixcontact.com/us/products/1732580>

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (assembly)  | -5 °C ... 100 °C  |
| Ambient temperature (operation) | -50 °C ... 110 °C |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

# SPT 2,5/11-V-5,0-EX - PCB terminal block


1732580

<https://www.phoenixcontact.com/us/products/1732580>



## Drawings

Drilling plan/solder pad geometry



# SPT 2,5/11-V-5,0-EX - PCB terminal block





1732580


<https://www.phoenixcontact.com/us/products/1732580>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1732580>

|  <b>cULus Recognized</b><br>Approval ID: E60425-20061129 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B   | 300 V                 | 20 A                  | 24 - 12           | -                           |
| D   | 150 V                 | 15 A                  | 24 - 12           | -                           |
| C   | 150 V                 | 20 A                  | 24 - 12           | -                           |

|  <b>ATEX</b><br>Approval ID: KEMA 07ATEX0193 U |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   | 176 V                 | 22 A                  | -                 | 0.2 - 4                     |

|  <b>IECEx</b><br>Approval ID: IECEx KEM 07.0057U |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   | 176 V                 | 22 A                  | -                 | 0.2 - 4                     |

# SPT 2,5/11-V-5,0-EX - PCB terminal block



1732580

<https://www.phoenixcontact.com/us/products/1732580>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460101 |
| ECLASS-15.0 | 27460101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002643 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SPT 2,5/11-V-5,0-EX - PCB terminal block



1732580

<https://www.phoenixcontact.com/us/products/1732580>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.151 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)