

PP-RJ-RJ-E - Patch panel



1746811

<https://www.phoenixcontact.com/us/products/1746811>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch panel, two RJ45 jacks, CAT6, 10/100/1000 Mbps, DIN rail adapter, IP20, IECEx and ATEX approvals, shipbuilding approval in accordance with DNV

Product description

This product is the successor to FL-PP-RJ45/RJ45, item no. 2901646. Ethernet patch panels enable quick and easy connection between the field cabling and control cabinet cabling. The passive termination panels are a convenient alternative to the on-site assembly of RJ45 connectors.

Your advantages

- 10/100/1000 Mbps, CAT6
- Extended temperature range of -40 °C ... +75 °C
- Shipbuilding approval in accordance with DNV
- PoE-capable in accordance with IEEE 802.3bt, type 4

Commercial data

Item number	1746811
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	DN07
Product key	DNC334
GTIN	4067923309487
Weight per piece (including packing)	62.9 g
Weight per piece (excluding packing)	57.63 g
Customs tariff number	85366990
Country of origin	DE

PP-RJ-RJ-E - Patch panel



1746811

<https://www.phoenixcontact.com/us/products/1746811>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Product properties

Product type	Patch panel
MTTF	105699 Years

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Maximum power dissipation for nominal condition	0 W (passive module, no supply voltage required)
Rated insulation voltage	85 V DC (In accordance with EN/IEC 60079-7, Annex H)

Interfaces

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Serial transmission speed	10/100/1000 Mbps
Frequency range	250 MHz
Connection method	RJ45 jack
Note on the connection method	CAT6
Pin assignment	1:1
Transmission length	100 m (including patch cables)
Transmission medium	Copper
Output nominal voltage	< 57 V DC
Maximum output power	60 W
Maximum output current	725 mA (Per channel)

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Connection method	RJ45 jack
-------------------	-----------

Dimensions


PP-RJ-RJ-E - Patch panel

1746811

<https://www.phoenixcontact.com/us/products/1746811>



Dimensional drawing



Width	23.8 mm
Height	101.3 mm
Depth	50 mm

Material specifications

Color (Housing)	light gray (RAL 7035)
Material (Housing)	Plastic
Flammability rating according to UL 94	V0

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 10 Hz ... 57 Hz, amplitude ± 3.5 mm, 57 Hz ... 150 Hz, 5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 30g for 11 ms, three shocks in each spatial direction
Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 10g for 16 ms, 1000 shocks in each spatial direction

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Manufacturer's declaration)
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation) ≤ 2000 m (Restrictions for ATEX applications)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

IECEX

Identification	Ex ec IIC Gc
Certificate	IECEX IBE 25.0006U

ATEX

Identification	Ex II 3 G Ex ec IIC Gc
Certificate	IBExU25ATEXB001 U

PP-RJ-RJ-E - Patch panel



1746811

<https://www.phoenixcontact.com/us/products/1746811>

Note	Please follow the special installation instructions in the documentation!
------	---

UL, USA

Certificate	UL 60079-0 Ed. 6 / UL 60079-15 Ed. 4
-------------	--------------------------------------

UL, Canada

Certificate	CSA 22.2 No. 60079-0 Ed. 3 / CSA 22.2 No. 60079-15:16
-------------	---

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

Shipbuilding

Identification	DNV
----------------	-----

Shipbuilding data

Temperature	D
Humidity	B
Vibration	B
EMC	B

Mounting

Mounting type	DIN rail mounting
Assembly note	The product can be snapped onto all 35 mm DIN rails in accordance with EN/IEC 60715.
Useable DIN rail type	DIN rail: 35 mm

PP-RJ-RJ-E - Patch panel


1746811

<https://www.phoenixcontact.com/us/products/1746811>



Drawings

Dimensional drawing



Compact housing


PP-RJ-RJ-E - Patch panel

1746811

<https://www.phoenixcontact.com/us/products/1746811>



Schematic diagram



Front view


PP-RJ-RJ-E - Patch panel

1746811

<https://www.phoenixcontact.com/us/products/1746811>




Schematic diagram



Mounting on a DIN rail

Schematic diagram



Removal


PP-RJ-RJ-E - Patch panel

1746811

<https://www.phoenixcontact.com/us/products/1746811>



Circuit diagram



PP-RJ-RJ-E - Patch panel



1746811

<https://www.phoenixcontact.com/us/products/1746811>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1746811>



cULus Listed

Approval ID: E238705



DNV GL

Approval ID: TAA00001KR_7



IECEx

Approval ID: IECEx IBE 25.0006U



ATEX

Approval ID: IBExU25ATEXB001 U



cULus Listed

Approval ID: E366272

PP-RJ-RJ-E - Patch panel



1746811
<https://www.phoenixcontact.com/us/products/1746811>

Classifications

ECLASS

ECLASS-13.0	19170112
ECLASS-15.0	19170112

ETIM

ETIM 10.0	EC001128
-----------	----------

PP-RJ-RJ-E - Patch panel



1746811
<https://www.phoenixcontact.com/us/products/1746811>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com