

ES-FT-HSC20-P-25 01 AG - Connector



1762206

<https://www.phoenixcontact.com/us/products/1762206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stacked connector, female connector metal terminal block, silver-plated, suitable for 25 mm² wiring

Commercial data

Item number	1762206
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB04
Product key	ABLDBA
GTIN	4067923370593
Weight per piece (including packing)	10.21 g
Weight per piece (excluding packing)	10 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Product properties

Product type	Connectors for energy storage
Product family	HSC
Number of positions	4

Electrical properties

Rated surge voltage	8 kV
Rated current	100 A
Insulation resistance	1000 MΩ

Connection data

Connection method	Crimp
-------------------	-------

Material specifications

Color	silver
Contact surface	Ag

Cable/line

Cable cross section	25 mm ²
---------------------	--------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (incl. temperature increase)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 4000 m

Standards and regulations

Standards/specifications	TÜV (PPP 51090B)
	UL 4128

1762206

<https://www.phoenixcontact.com/us/products/1762206>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

1762206

<https://www.phoenixcontact.com/us/products/1762206>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com