

CSS 7.5-3/3-EMC - Speed starter

1721227

<https://www.phoenixcontact.com/us/products/1721227>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 7.5 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, with integrated EMC filter and braking resistor connection

Commercial data

Item number	1721227
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C473
Product key	DK7322
GTIN	4067923274204
Weight per piece (including packing)	2,586 g
Weight per piece (excluding packing)	2,586 g
Customs tariff number	85371098
Country of origin	CN

Technical data

Product properties

Product type	Speed starter
Product family	CONTACTRON
Operating elements	Push button
	Rotary switch

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Number of phases	3
------------------	---

Input data

Mains

Number of phases	3
Input voltage	380 V AC
	400 V AC
	480 V AC
Input voltage range	220 V AC ... 480 V AC -15 % ... +10 %
Frequency range	47 Hz ... 63 Hz
Nominal current	19.7 A (no line reactor)
	13.8 A (with line reactor)

Output data

Nominal motor power	7.5 kW
Apparent power	12 kVA
Nominal output current (I_N)	17 A (4 kHz)
	11.6 A (8 kHz)
	6 A (16 kHz)
Output frequency	0 Hz ... 500 Hz
Power dissipation	134 W (2 kHz)
	141.1 W (4 kHz)
	131.9 W (8 kHz)
	121.4 W (16 kHz)
	19 W (stand by)
Output current	≤ 25.5 A (180 s)
	≤ 12.75 A (180 s, during recovery time)
	≤ 30.6 A (15 s)
	≤ 8.5 A (15 s, during recovery time)
Recovery time	150 s (180 s)
	12 s (15 s)

CSS 7.5-3/3-EMC - Speed starter



1721227

<https://www.phoenixcontact.com/us/products/1721227>

Overload time	30 s (180 s)
	3 s (15 s)
Discharge time	3 min (Intermediate circuit capacitors)

Switching

Output name	Relay output
Contact switching type	1 changeover contact
Maximum switching voltage	125 V AC
	30 V DC
Maximum inrush current	3 A
Inrush current, minimum	10 mA (5 V DC)

Connection data

Power-level terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Conductor cross-section flexible	0.2 mm ² ... 6 mm ²
	0.2 mm ² ... 4 mm ² (with ferrule)
Conductor cross-section AWG	24 ... 10

Control terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
	0.2 mm ² ... 0.75 mm ²
Conductor cross-section AWG	24 ... 16

Dimensions

Drill hole

Diameter	5.5 mm
Width	110 mm
Height	210 mm
Depth	200 mm
Length	≤ 30 m (Motor cable length (EMC compliance category C3))
	≤ 50 m (Motor cable length (no EMC compliance))

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection (IP)	IP20
---------------------------	------

CSS 7.5-3/3-EMC - Speed starter



1721227

<https://www.phoenixcontact.com/us/products/1721227>

Degree of protection (NEMA)	NEMA 1
Ambient temperature (operation)	-20 °C ... 55 °C (without current derating)
	-20 °C ... 60 °C (with linear current derating)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	≤ 2000 m
	> 2000 m (with derating)
Permissible humidity (operation)	90 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)
Air pressure (operation)	86 kPa ... 106 kPa
Air pressure (storage/transport)	70 kPa ... 106 kPa

Approvals

Safety Integrity Level (SIL, IEC 61800-5-2)

Identification	3
----------------	---

Performance Level (EN ISO 13849)

Identification	e
----------------	---

Category (ISO 13849)

Identification	4
----------------	---

Standards and regulations

Standards/regulations	IEC 61800-5-1
	IEC 61800-3

Mounting

Mounting type	DIN rail mounting
	Panel mounting

CSS 7.5-3/3-EMC - Speed starter



1721227

<https://www.phoenixcontact.com/us/products/1721227>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1721227>



cULus Listed

Approval ID: E322526

CSS 7.5-3/3-EMC - Speed starter



1721227

<https://www.phoenixcontact.com/us/products/1721227>

Classifications

ECLASS

ECLASS-13.0	27142320
ECLASS-15.0	27142320

ETIM

ETIM 10.0	EC000256
-----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
	Bis(2-(2-methoxyethoxy)ethyl)ether(CAS: 143-24-8)