

HC-A 3-ESTS - Contact insert

1773080

<https://www.phoenixcontact.com/us/products/1773080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON male insert, A3 series, 3-pos., screw connection without wire protection



Commercial data

Item number	1773080
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF61
Product key	AF7ABB
GTIN	4017918122300
Weight per piece (including packing)	16.24 g
Weight per piece (excluding packing)	16.24 g
Customs tariff number	85366990
Country of origin	DE

HC-A 3-ESTS - Contact insert

1773080

<https://www.phoenixcontact.com/us/products/1773080>

Technical data

Mounting

Assembly note	Connectors may be operated only when there is no load/voltage.
---------------	--


Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-A
Type	D7
Number of positions	3
Connection profile	3+PE
Contact numbering	1 - 3

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Height	25 mm

Connection data

Connection technology

Connection technology	Screw connection
Connection in acc. with standard	IEC / EN

Conductor connection

Conductor cross-section	0.5 mm ² ... 1.5 mm ² (applies to stranded conductors with ferrules)
Connection cross section AWG	20 ... 16
Tightening torque	0.25 Nm
Stripping length of the individual wire	5 mm

Electrical properties

Rated voltage (III/3)	230 V (Conductor-PE)
	400 V (Conductor-Conductor)
Rated voltage for power contacts	230/400 V
Rated surge voltage	4 kV
Rated current	16 A
Test voltage	4 kV AC

HC-A 3-ESTS - Contact insert



1773080

<https://www.phoenixcontact.com/us/products/1773080>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

Standards and regulations

Constructional and testing regulations	DIN VDE 0627/86
	DIN VDE 0110/02.79
	DIN VDE 0110-1/04.97
	IEC 60664-1, DIN IEC 60512
	IEC 60352
Tests	DIN VDE 0627/86
	DIN VDE 0110/02.79
	DIN VDE 0110-1/04.97
	IEC 60664-1, DIN IEC 60512
	IEC 60352


HC-A 3-ESTS - Contact insert

1773080

<https://www.phoenixcontact.com/us/products/1773080>





Drawings



Male insert

Schematic diagram




Connector pin assignment connection side: Left pin; right socket

HC-A 3-ESTS - Contact insert

1773080

<https://www.phoenixcontact.com/us/products/1773080>



Derating diagram: Series HC-A 3-E..S / HC-A 4-E..S

HC-A 3-ESTS - Contact insert

1773080

<https://www.phoenixcontact.com/us/products/1773080>



Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

HC-A 3-ESTS - Contact insert



1773080

<https://www.phoenixcontact.com/us/products/1773080>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com