

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distribution block, nom. voltage: 1000 V, nominal current: 232 A, Thermal continuous current  $I_{th}$ : 250 A, number of connections: 12, number of positions: 1, connection method: Screw connection, Rated cross section: 95 mm<sup>2</sup>, Line contact, cross section: 35 mm<sup>2</sup> - 120 mm<sup>2</sup>, Screw connection, Load contact, cross section: 2.5 mm<sup>2</sup> - 35 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, Direct mounting, color: dark gray

## Your advantages

- Fast installation via ready-to-connect distributor and collection block
- Blocks can be snapped to each other to form function groups
- As well as saving space, the compact design enables user-friendly wiring in a small amount of space
- Flexible use, thanks to DIN rail and direct mounting
- Reversible cover for optimum readability of the technical data

## Commercial data

Item number	1725169
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE05
Product key	BEK825
GTIN	4067923280717
Weight per piece (including packing)	443.3 g
Weight per piece (excluding packing)	443.3 g
Customs tariff number	85369010
Country of origin	IN

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Technical data

### Notes

#### General

Note	The maximum load current of a single clamping unit must not be exceeded.
	For power distribution applications, IEC 60364-4-43:2008; modified + corrigendum Okt. 2008 (DIN VDE 0100-430:2010-10) section 433.2 ff must be observed!

### Product properties

Product type	Distributor terminal block
Product family	TB
Area of application	Machine building
Number of positions	1
Number of connections	12
Number of rows	1

#### Insulation characteristics

Degree of pollution	3
---------------------	---

### Electrical properties

Rated surge voltage	8 kV
---------------------	------

### Connection data

Number of connections per level	12
Nominal cross section	95 mm <sup>2</sup>
Rated cross section AWG	000

#### Line contact

Connection method	Screw connection
Screw thread	M14
Number of connections	1
Note	Ferrules are mandatory when using flexible conductors
Tightening torque	19 ... 21 Nm
Stripping length	28 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	35 mm <sup>2</sup> ... 120 mm <sup>2</sup>
Cross section AWG	0 ... 000 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	35 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Nominal cross section	95 mm <sup>2</sup>
Thermal continuous current $I_{th}$	250 A
Nominal current	232 A
Nominal voltage	1000 V AC (suitable for 1500 V DC)

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Load contact

Connection method	Screw connection
Screw thread	M8
Number of connections	2
Note	Ferrules are mandatory when using flexible conductors
Tightening torque	3.5 ... 5 Nm
Stripping length	11 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Cross section AWG	12 ... 2 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>

## Load contact

Connection method	Screw connection
Screw thread	M6
Number of connections	5
Note	Ferrules are mandatory when using flexible conductors
Tightening torque	2 ... 3 Nm
Stripping length	11 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	2.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>
Cross section AWG	12 ... 6 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>

## Load contact

Connection method	Screw connection
Screw thread	M6
Number of connections	4
Note	Ferrules are mandatory when using flexible conductors
Tightening torque	2 ... 3 Nm
Stripping length	11 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	2.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section AWG	12 ... 8 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>

## Dimensions

Width	46.2 mm
Height	96 mm
Depth	60 mm
Depth on NS 35/7,5	61.5 mm
Depth on NS 35/15	69 mm

## Material specifications

Color	basalt gray (RAL 7012)
-------	------------------------

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

Flammability rating according to UL 94	V0
Insulating material group	I
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

## Electrical tests

### Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

### Temperature-rise test

Requirement temperature-rise test	Increase in temperature $\leq 45$ K
Result	Test passed
Short-time withstand current 95 mm <sup>2</sup>	11.4 kA
Result	Test passed

### Power-frequency withstand voltage

Test voltage setpoint	3.82 kV
Result	Test passed

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Mechanical tests

### Mechanical strength

Result	Test passed
--------	-------------

### Attachment on the carrier

DIN rail/fixing support	NS 35
Result	Test passed

### Test for conductor damage and slackening

Rotation speed	9 rpm
Revolutions	135
Conductor cross-section/weight	2.5 mm <sup>2</sup> / 0.7 kg
	16 mm <sup>2</sup> / 2.9 kg
	35 mm <sup>2</sup> / 6.8 kg
	120 mm <sup>2</sup> / 14 kg
Result	Test passed

## Environmental and real-life conditions

### Needle-flame test

Time of exposure	5 s
Result	Test passed

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Ambient conditions

Degree of protection	IP10
Ambient temperature (operation)	-40 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Standards and regulations


Connection in acc. with standard	IEC 60947-7-1
	IEC 60947-7-1
	IEC 60947-7-1
	IEC 60947-7-1

## Mounting

Mounting type	NS 35/7,5
	NS 35/15
	Direct mounting

## Drawings

Circuit diagram



# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1725169>



**UL Recognized**

Approval ID: E60425



**CSA**

Approval ID: 80247697

# TB-EE-DB 250/1+11 - Distribution block



1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Classifications

### ECLASS

ECLASS-13.0	27250118
ECLASS-15.0	27250118

### ETIM

ETIM 10.0	EC000897
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1725169

<https://www.phoenixcontact.com/us/products/1725169>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)