


REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling relay with force-guided contacts in accordance with DIN EN 61810-3, contact switching type: 6 changeover contacts, multi-layer gold contact. The requirements for type A in accordance with DIN EN 61810-3 are satisfied if the circuit is designed as 5 N/O contacts / 1 N/C contact.

Commercial data

Item number	1779558
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	C465
Product key	DK69DE
GTIN	4067923397309
Weight per piece (including packing)	25.68 g
Weight per piece (excluding packing)	23 g
Customs tariff number	85364110
Country of origin	CN

REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Technical data

Product properties

Product type	Single relay
Application	Forcibly guided contacts
Set comprises	1732886 RIF-RPT-LDP-24DC/1X2/5X1/AU/FG
Operating mode	100% operating factor
Mechanical service life	approx. 10^7 cycles

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Insulation characteristics: Air clearances and creepage distances between coil and contact side

Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	27.07.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.5 W
Test voltage	4 kV _{rms} (50 Hz, 1 min.)
	2.5 kV _{rms} (50 Hz, 1 min.)
	1.5 kV _{rms} (50 Hz, 1 min.)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
Rated surge voltage	4 kV

Air clearances and creepage distances between coil and contact side

Rated insulation voltage	250 V AC
Rated surge voltage	6 kV

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	20.4 V DC ... 26.4 V DC
Input voltage range in reference to U_N	see diagram
Drive and function	monostable
Drive (polarity)	non-polarized
Typical input current at U_N	30 mA
Input power dissipation for U_N	0.72 W

REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Typical response time	15 ms
Typical release time	10 ms
Coil voltage	24 V DC
Protective circuit	Freewheeling diode
Status display	LED (yellow)

Output data

Switching

Contact switching type	2 changeover contacts, forcibly actuated
Type of switch contact	Single contact
Contact material	AgSnO ₂ , +AU
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Interrupting rating (ohmic load) max.	144 W (24 V DC)
	180 W (30 V DC)
	1500 VA (250 V AC)
Force-guided contacts in accordance with EN 61810-3	Type B

Dimensions

Item dimensions

Width	13 mm
Height	24 mm
Depth	50 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Relay)	RT II (Relay)
Degree of protection (Installation location)	IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m

Standards and regulations

Standards/regulations	EN 61810-1
	EN 61810-3

Air clearances and creepage distances between the power circuits

Standards/regulations	EN 60947-5-1
-----------------------	--------------

Air clearances and creepage distances between coil and contact side

Standards/regulations	EN 60947-5-1
-----------------------	--------------

Mounting

Mounting type	Plug-in mounting
---------------	------------------

REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Assembly note	in rows with zero spacing
Mounting position	any

REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

REL-SR- 24DC/5X1AU/1X2AU/FG - Coupling relay



1779558

<https://www.phoenixcontact.com/us/products/1779558>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com