

# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protective device, UL Listed type 1 and IEC type 2, for 3-phase power supply systems for 690Y/400 V AC, replaceable surge protection plugs with local status indicator (green/red), with plug-in remote signaling.

## Your advantages

- Universal surge protective device (SPD) with UL Listed type 1 and IEC type 2: suitable for all common supply system configurations and supply voltages in North America
- Minimal maintenance with replaceable surge protection plugs
- Clear status indication with local optical green/red display and plug-in remote signaling for quick and easy installation
- Simple planning with comprehensive digital data
- Miswiring and touch protection for safe installation

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1790783       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL17          |
| Product key                          | CL138U        |
| GTIN                                 | 4067923410480 |
| Weight per piece (including packing) | 418.3 g       |
| Weight per piece (excluding packing) | 389.9 g       |
| Customs tariff number                | 85363030      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                                          |                                              |
|------------------------------------------|----------------------------------------------|
| Product type                             | Surge protection for NEMA power supply units |
| Product family                           | VAL-SPP                                      |
| IEC test classification                  | II                                           |
|                                          | T2                                           |
| EN type                                  | T2                                           |
| IEC power supply system                  | TN-C                                         |
| Type                                     | DIN rail module, two-section, divisible      |
| Distance between live and grounded parts | 1 mm                                         |
| Number of positions                      | 3                                            |
| End-of-life mode                         | OCM                                          |
| Surge protection fault message           | Optical, remote indicator contact            |
| Number of ports                          | One                                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |

### Electrical properties

|                         |               |
|-------------------------|---------------|
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |
|-------------------------|---------------|

### Indicator/remote signaling

|                            |                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------|
| Connection name            | Remote fault indicator contact                                                       |
| Switching function         | Changeover contact                                                                   |
| Max. required back-up fuse | 1 A (gG)                                                                             |
| AC operating voltage       | 5 V AC ... 250 V AC                                                                  |
| AC operating current       | 5 mA AC ... 1 A AC                                                                   |
| DC operating voltage       | 30 V DC                                                                              |
| DC operating current       | 1 A DC                                                                               |
| DC operating voltage       | 125 V DC                                                                             |
| DC operating current       | 200 mA DC                                                                            |
| Insulation type            | The product has double/reinforced insulation between the main and auxiliary circuit. |

### Connection data

|                                  |                                                                  |
|----------------------------------|------------------------------------------------------------------|
| Connection method                | Screw connection                                                 |
| Screw thread                     | M5                                                               |
| Tightening torque                | 3 Nm ... 3.5 Nm                                                  |
| Stripping length                 | 18 mm                                                            |
| Conductor cross-section flexible | 1.5 mm² ... 35 mm² (without ferrule)                             |
|                                  | 2x 1.5 mm² ... 16 mm² (2 conductors with the same cross-section) |
| Conductor cross-section rigid    | 1.5 mm² ... 50 mm²                                               |

# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

|                                                                                           |                                                                                          |
|-------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
|                                                                                           | 2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section) |
| Conductor cross-section AWG                                                               | 15 ... 2                                                                                 |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>                                               |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve                      | 1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>                                               |
|                                                                                           | 2x 1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> (2 conductors with the same cross-section) |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve                   | 1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>                                               |
|                                                                                           | 2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section) |
| Connection method                                                                         | Fork-type cable lug                                                                      |
| Conductor cross-section flexible                                                          | 1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>                                               |

## Remote fault indicator contact

|                                                                         |                                               |
|-------------------------------------------------------------------------|-----------------------------------------------|
| Connection method                                                       | Push-in connection                            |
| Stripping length                                                        | 8 mm                                          |
| Conductor cross-section flexible                                        | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section rigid                                           | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section AWG                                             | 24 ... 16                                     |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve    | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |

## Dimensions

|                     |                                 |
|---------------------|---------------------------------|
| Dimensional drawing |                                 |
| Width               | 53.4 mm                         |
| Height              | 109.1 mm                        |
| Depth               | 71.5 mm (incl. DIN rail 7.5 mm) |
| Horizontal pitch    | 3 Div.                          |

## Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color                                  | gray (RAL 7042)       |
|                                        | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V-0                   |
| CTI value of material                  | 600                   |
| Insulating material                    | PA 6.6-FR 20 % GF     |
|                                        | PBT                   |
| Material group                         | I                     |
| Housing material                       | PA 6.6-FR 20 % GF     |
|                                        | PBT                   |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Protective circuit

|                                                |                                                                           |
|------------------------------------------------|---------------------------------------------------------------------------|
| Mode of protection                             | L-PEN                                                                     |
| Nominal voltage $U_N$                          | 400/690 V AC $\pm 10\%$ (TN-C)<br>347/600 V AC $\pm 10\%$ (TN-C)          |
| Nominal frequency $f_N$                        | 50 Hz (60 Hz)                                                             |
| Maximum continuous operating voltage $U_C$     | 550 V AC                                                                  |
| Rated load current $I_L$                       | 80 A (25 mm <sup>2</sup> )                                                |
| Standby power consumption $P_C$                | $\leq 495$ mVA                                                            |
| Nominal discharge current $I_n$ (8/20) $\mu$ s | 20 kA                                                                     |
| Short-circuit current rating $I_{SCCR}$        | 25 kA                                                                     |
| Voltage protection level $U_p$                 | $\leq 2.4$ kV                                                             |
| Residual voltage $U_{res}$                     | $\leq 2.4$ kV (at $I_n$ )                                                 |
| TOV behavior at $U_T$                          | 581 V AC (5 s / withstand mode)<br>762 V AC (120 min / safe failure mode) |
| Response time $t_A$                            | $\leq 25$ ns                                                              |
| Max. backup fuse with V-type through wiring    | 80 A (gG)                                                                 |
| Max. backup fuse with branch wiring            | 250 A (gG)                                                                |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                           |
|-----------------------------------------|-----------------------------------------------------------|
| Degree of protection                    | IP20C (Installed)                                         |
| Ambient temperature (operation)         | -40 °C ... 85 °C                                          |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                                          |
| Ambient temperature (assembly)          | -5 °C ... 50 °C                                           |
| Altitude                                | $\leq 2000$ m (amsl)                                      |
| Permissible humidity (operation)        | 5 % ... 95 %                                              |
| Shock (operation)                       | 25g (Half-sine / 11 ms / 3x $\pm X$ , $\pm Y$ , $\pm Z$ ) |
| Vibration (operation)                   | 5g (10 ... 500 Hz / 2.5 h / X, Y, Z)                      |

## Approvals

### UL specifications

|                                                 |                        |
|-------------------------------------------------|------------------------|
| Maximum continuous operating voltage MCOV (L-L) | 1100 V AC              |
| Maximum continuous operating voltage MCOV (L-G) | 550 V AC               |
| Short-circuit current rating (SCCR)             | 200 kA                 |
| Voltage protection rating VPR (L-L)             | 4000 V                 |
| Voltage protection rating VPR (L-G)             | 2000 V                 |
| Nominal discharge current $I_n$                 | 20 kA                  |
| Maximum Surge Current per Phase                 | 1x 40 kA (IEEE C62.73) |

# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

|                           |                    |
|---------------------------|--------------------|
| Mode of protection        | L-L                |
|                           | L-G                |
| Nominal voltage           | 400/690 V AC (Wye) |
|                           | 347/600 V AC (Wye) |
| Power distribution system | Wye                |
| Nominal frequency         | 50/60 Hz           |
| SPD Type                  | 1                  |

## UL indicator/remote signaling

|                      |                    |
|----------------------|--------------------|
| Operating voltage    | 250 V AC           |
| DC operating voltage | 30 V DC            |
| AC operating current | 5 mA AC ... 1 A AC |
| DC operating current | 1 A DC             |

## UL connection data

|                             |                         |
|-----------------------------|-------------------------|
| Tightening torque           | 30 lb <sub>f</sub> ·in. |
| Conductor cross-section AWG | 14 ... 2                |

## Standards and regulations


|                          |                 |
|--------------------------|-----------------|
| Standards/specifications | IEC 61643-11    |
| Note                     | 2011            |
| Standards/specifications | EN 61643-11     |
| Note                     | 2012 + A11:2018 |

## Mounting


|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

## Drawings

Dimensional drawing



Circuit diagram



# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1790783>



**cULus Listed**

Approval ID: E330181-20251028

# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171202 |
| ECLASS-15.0 | 27171202 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000941 |
|-----------|----------|

# VAL-US-SPP-400/40/3+0-R - Surge protection device



1790783

<https://www.phoenixcontact.com/us/products/1790783>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                                                               |
|-------------------------------------|---------------------------------------------------------------|
| REACH candidate substance (CAS No.) | Benzene-1,2,4-tricarboxylic acid 1,2 anhydride(CAS: 552-30-7) |
|-------------------------------------|---------------------------------------------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)