

UKK 3-MSTB-5,08-F - Double-level terminal block



1785832

<https://www.phoenixcontact.com/us/products/1785832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double-level terminal block, for MSTB flange plug screw connection, pitch: 5.08 mm, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

Commercial data

Item number	1785832
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1241
GTIN	4017918042080
Weight per piece (including packing)	5.6 g
Weight per piece (excluding packing)	5.6 g
Customs tariff number	85389099
Country of origin	PL

UKK 3-MSTB-5,08-F - Double-level terminal block



1785832

<https://www.phoenixcontact.com/us/products/1785832>

Technical data

Product properties

Product type	Flange
Product family	UKK 3-MSTB
Number of positions	1
Pitch	5.08 mm
Number of rows	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Maximum power dissipation for nominal condition	0 W
---	-----

Dimensions

Width	5.08 mm
End cover width	2.5 mm
Height	50 mm
Depth on NS 35/7,5	53.5 mm
Length	50 mm
Pitch	5.08 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Contact surface	Tin Sn

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

	NS 35/7,5
--	-----------

UKK 3-MSTB-5,08-F - Double-level terminal block



1785832

<https://www.phoenixcontact.com/us/products/1785832>

Mounting type	NS 35/15
	NS 32

UKK 3-MSTB-5,08-F - Double-level terminal block



1785832

<https://www.phoenixcontact.com/us/products/1785832>

Classifications

ECLASS

ECLASS-13.0	27250302
ECLASS-15.0	27250302

ETIM

ETIM 10.0	EC001041
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UKK 3-MSTB-5,08-F - Double-level terminal block



1785832

<https://www.phoenixcontact.com/us/products/1785832>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.026 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com