

# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic contact insert, Range of articles: VARIOCON, design: FSMA, color: light gray, number of positions: 1

## Your advantages

- Clear overview
- For a variety of applications

## Commercial data

Item number	1855432
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB01
Product key	ABLACA
GTIN	4017918162696
Weight per piece (including packing)	16.1 g
Weight per piece (excluding packing)	9.512 g
Customs tariff number	85367000
Country of origin	PL

## Technical data

### Notes

#### Safety note

<p>Safety note</p>	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"> <li>• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li> <li>• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li> <li>• The products are suitable for applications in plant, controller, and electrical device engineering.</li> <li>• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.</li> <li>• Assembled products may not be manipulated or improperly opened.</li> <li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li> <li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li> <li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li> <li>• Ensure that the protective or functional ground has been properly connected.</li> <li>• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector</li> <li>• Observe the corresponding technical data. You will find information:             <ul style="list-style-type: none"> <li>o On the product</li> <li>o On the packing label</li> <li>o In the supplied documentation</li> <li>o Online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> under the product</li> </ul> </li> <li>• Only use tools recommended by Phoenix Contact</li> <li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li> <li>• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a></li> <li>• Operate the connector only when it is fully plugged in.</li> <li>• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the</li> </ul>
--------------------	---

# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

	standards.
	<ul style="list-style-type: none"><li>• Observe the minimum bending radius of the cable. Lay the cable without twisting it.</li></ul>
	<ul style="list-style-type: none"><li>• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).</li></ul>


## Product properties

Product type	Fiber optic connector (cable side)
Product family	VARIOCON
Type	FSMA
Number of positions	1
Connection profile	F-SMA type 905, IEC 874-2

## Electrical properties

Attenuation	≤ 1.5 dB (at 650 nm (for each plug))
-------------	--------------------------------------

## Dimensions

Dimensional drawing	
Width	7 mm
Height	7 mm
Length	26 mm

## Mechanical characteristics

Contact diameter	3.1 mm
------------------	--------

## Material specifications

Color	light gray
Material Housing	Nickel silver
Material Contact	Nickel silver
Material Screw connection	CuZn

## Cable/line

Cable type	Polymer fiber (980 / 1000 μm)
External cable diameter	≤ 2.30 mm
Stripping length of the individual wire	12 mm
Resistance to oil	yes
Flame resistance	yes

## FO cable

Number of fibers	2
Fiber	Polymer fiber, 980/1000 μm
Fiber type	POF fiber A4A

# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

Transmission medium	FO
---------------------	----

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Characteristics

Attenuation	≤ 1.5 dB (at 650 nm (for each plug))
-------------	--------------------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Resistance to oil	yes

## Standards and regulations

Flame resistance	yes
Resistance to oil	yes


# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

## Drawings



# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

## Classifications

### ECLASS

ECLASS-13.0

27440192

### ETIM

ETIM 9.0

EC002943

### UNSPSC

UNSPSC 21.0

39121400

# VC-FSMA-M-2 SET - Fiber optic contact insert



1855432

<https://www.phoenixcontact.com/us/products/1855432>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)