

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, straight, M23, number of positions: 4+2+4+PE / 3+N+PE, contact connection type: Pin, Wave soldering, series: SH, partially assembled, only suitable for use with the M23 hybrid solder-in connector

Figure shows fully assembled variant

Your advantages

- Reliable transmission of signals, data, and power in a single connector
- 80% faster assembly and 60% less installation space compared to litz wire assemblies
- Cost reduction due to the elimination of additional PCB connectors
- Reduction of PCB complexity and EMC risks
- Elimination of work steps with high error potential

Commercial data

Item number	1835953
Packing unit	48 pc
Minimum order quantity	48 pc
Sales key	AB38
Product key	ABRCDX
GTIN	4067923477490
Weight per piece (including packing)	29.99 g
Weight per piece (excluding packing)	29.99 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Safety note

Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- Only use tools recommended by Phoenix Contact

- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.

- Operate the connector only when it is fully plugged in and interlocked.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Product properties

Product type	Contact insert
Series	SH
Application	Hybrid
Number of positions	11
Connection profile	4+2+4+PE / 3+N+PE
Thread type	M23

Electrical properties

Contact: Power contacts

Contact diameter	2 mm
Nominal current I_N	30 A (for max. connection cross section)
Nominal voltage U_N	630 V AC (Overvoltage category III/3)
	800 V DC (Overvoltage category II/3)
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact: Data contacts

Contact diameter	0.8 mm
Nominal current I_N	3.6 A (for max. connection cross section)
Nominal voltage U_N	50 V (Contact 5 ... 8)
Overvoltage category	II, III
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Signal contacts

Contact diameter	1 mm
Nominal current I_N	8 A (for max. connection cross section)
Nominal voltage U_N	50 V (Contact 1 and 2)
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Wave soldering
-------------------	----------------

Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

Connector

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Type	straight
------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----


Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-40 °C ... 115 °C (see derating curve)
Altitude	2000 m (4000 m at 300 V system voltage in accordance with DIN EN 60664-1)
Permissible humidity (storage/transport)	50 % ... 65 %

Drawings

Schematic diagram




Pin assignment CAT5 pin, partially assembled




Classification wave soldering profile

Diagram




I = current strength, θ = ambient temperature, power contacts A-B: 2.5 mm², 2 x 22 A, power contacts C-D: 2.5 mm², 2 x 13 A (constant), signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)

Diagram



I = current strength, θ = ambient temperature, power contacts A-C: 2.5 mm², 3 x 26 A, signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)



I = current strength, ϑ = ambient temperature, power contacts A-D: 2.5 mm², 4 x 20 A, signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1835953>



cUL Recognized
Approval ID: E468743



UL Recognized
Approval ID: E468743

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

SH-8EPC5-PCB-L4-ABCD-PE-12 - Contact insert



1835953

<https://www.phoenixcontact.com/us/products/1835953>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com