HC-DCC4-I-CT-M 100 - Contact insert

1887970

https://www.phoenixcontact.com/us/products/1887970

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 4+PE, size: DCC06, Pin, Crimp connection, 690 V, 100 A, 6 mm^2 ... 25 mm^2, application: Power supply in data centers, tool-free Click-in mounting, Packing unit: 100 pcs

Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

Item number	1887970
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABL
GTIN	4067923557154
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Notes

General	Connectors may be operated only when there is no load/voltage.

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
	Tool-free snap-in into the plastic housings of the HC-DDC06 series


Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-DCC
Application	Power supply in data centers
Number of positions	4
Connection profile	4+PE
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	35.1 mm
Height	48.7 mm
Length	54.2 mm

Mechanical characteristics

Contact diameter	6 mm

Connection data

Connection technology

Connection technology	Crimp connection

Conductor connection

Conductor cross-section	6 mm² ... 25 mm²
Connection cross section AWG	10 ... 4

Electrical properties

Rated voltage (III/3)	690 V
Rated surge voltage	6 kV
Rated current	100 A
SCCR	65 kA (UL 2237)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Contact carrier material	PA 6


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)


Drawings

Dimensional drawing




Dimensional drawing

Schematic diagram



Connector pin assignment, connection side

Diagram



Derating diagram

Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 10.0	EC000438

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com