

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, number of connections: 8, connection method: Spade connection, Rated cross section: 4 mm², 1 level, cross section: 0.5 mm² - 6 mm², mounting type: NS 32, NS 35/7,5, NS 35/15, color: gray

Your advantages

- The slotted plugs enable one fully insulated or two bare 2.8 mm slip-on sleeves to be slid on in place of one 6.3 mm slip-on sleeve
- The housing panels only protrude slightly beyond the metal parts because it is assumed that fully-insulated slip-on sleeves are connected
- The front slip-on plug-in connection is the ideal wiring design for applications where space is limited and cable ducts need to be moved close to the terminal strip

Commercial data

Item number	1953017
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE05
Product key	BE511X
GTIN	4017918052508
Weight per piece (including packing)	11.24 g
Weight per piece (excluding packing)	10.99 g
Customs tariff number	85369010
Country of origin	PL

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Technical data

Product properties

Product type	Feed-through terminal block
Product family	UVKB
Number of connections	8
Number of rows	2
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	8
Nominal cross section	4 mm ²

1 level

Connection method	Spade connection
Spade connection	6.3/2.8 x 0.8 mm
Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Cross section AWG	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
Nominal cross section	4 mm ²
Nominal current	32 A (dependent on the slip-on connection sleeve)
Maximum load current	32 A (dependent on the slip-on connection sleeve)
Nominal voltage	800 V (voltage data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)

Dimensions

Width	6.2 mm
End cover width	2.2 mm
Height	68 mm
Depth on NS 32	49 mm
Depth on NS 35/7,5	44 mm
Depth on NS 35/15	51.5 mm

Material specifications

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 32
	NS 35/7,5
	NS 35/15

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block




1953017

<https://www.phoenixcontact.com/us/products/1953017>

Drawings

Circuit diagram




UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Circuit diagram



- 1 = cover
- 2 = fixed bridge
- 3 = insertion bridge
- 4 = isolator bridge bar
- 5 = bridge bar isolator
- 6 = separating plate
- 7 = partition plate
- 8 = test plug socket

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block





1953017


<https://www.phoenixcontact.com/us/products/1953017>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1953017>

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C				
	300 V	25 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00541				
---	--	--	--	--

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C				
	300 V	25 A	-	-

DNV Approval ID: TAE00001CT				
---------------------------------------	--	--	--	--

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UVKB 4-FS/FS(8-2,8-0,8) - Feed-through terminal block



1953017

<https://www.phoenixcontact.com/us/products/1953017>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.08 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com