

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header



1999466

<https://www.phoenixcontact.com/us/products/1999466>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the standard item

PCB headers, nominal cross section: 1.5 mm², color: black, contact surface: Au, contact connection type: Pin, number of potentials: 7, number of rows: 1, number of positions: 7, number of connections: 7, product range: SMC 1,5/..-G-HT, pitch: 3.81 mm, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 3.4 mm, number of solder pins per potential: 1, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: without, mounting method: without, type of packaging: packed in cardboard

Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Designed for integration into the SMT soldering process
- Angled connection enables multi-row arrangement on the PCB
- Maximum flexibility when it comes to device design – one header for connectors with different connection technologies

Commercial data

Item number	1999466
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	AABTMA
GTIN	4017918981198
Weight per piece (including packing)	3.61 g
Weight per piece (excluding packing)	709 g
Country of origin	DE

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header



1999466

<https://www.phoenixcontact.com/us/products/1999466>

Technical data

Product properties

Product type	PCB headers
Product family	SMC 1,5/..-G-HT
Product line	COMBICON Connectors S
Number of positions	7
Pitch	3.81 mm
Number of connections	7
Number of rows	1
Number of potentials	7
Pin layout	Linear pinning
Solder pins per potential	1

Mounting

Mounting type	THR soldering
Pin layout	Linear pinning

Material specifications


Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Completely gold-plated
Metal surface contact area (top layer)	Gold (0.8 μ m - 1.4 μ m Au)
Metal surface contact area (middle layer)	Nickel (2 μ m - 4 μ m Ni)
Metal surface soldering area (top layer)	Gold (0.8 μ m - 1.4 μ m Au)
Metal surface soldering area (middle layer)	Nickel (2 μ m - 4 μ m Ni)

Material data - housing

Color (Housing)	black (9005)
Insulating material	PA
Insulating material group	IIIa
CTI according to IEC 60112	325
Flammability rating according to UL 94	V0

Dimensions

Dimensional drawing	
Pitch	3.81 mm

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header



1999466

<https://www.phoenixcontact.com/us/products/1999466>

Width [w]	28.06 mm
Height [h]	14.4 mm
Length [l]	13.1 mm
Installed height	11 mm
Solder pin length [P]	3.4 mm
Pin dimensions	0.8 x 0.8 mm

PCB design

Hole diameter	1.2 mm
---------------	--------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (dependent on the derating curve)

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Dry bag

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header




1999466

<https://www.phoenixcontact.com/us/products/1999466>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1999466>

 cULus Recognized Approval ID: E60425-20110128		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B		300 V	8 A	-	-
D		300 V	8 A	-	-

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header



1999466

<https://www.phoenixcontact.com/us/products/1999466>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 10.0	EC002637
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SMC 1,5/ 7-G-3,81 HT BK AU CP4 - PCB header



1999466

<https://www.phoenixcontact.com/us/products/1999466>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.049 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com