

UM-PRO PCB C-LOCK L1 BK - Locking

2200164

<https://www.phoenixcontact.com/us/products/2200164>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Locking element for locking the PCB onto UM-PRO housing at level 1



The figure shows the versions for PCB level 1

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2200164 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | AC13 |
| Product key | ACHDAZ |
| GTIN | 4046356547581 |
| Weight per piece (including packing) | 0.504 g |
| Weight per piece (excluding packing) | 0.5 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|----------------|------------------------------|
| Product type | Mounting material |
| Housing type | Press-drawn section housings |
| Housing type | Extruded profile housings |
| Housing series | UM-PRO |
| Product family | UM-PRO |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Glow-wire test

| | |
|------------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 125 °C |
| Test duration | 1 h |
| Force | 20 N |

Mechanical strength / tumbling barrel

| | |
|----------------|------------------------|
| Specification | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm |
| Frequency | 50 |

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

UM-PRO PCB C-LOCK L1 BK - Locking



2200164

<https://www.phoenixcontact.com/us/products/2200164>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200164>



UL Recognized

Approval ID: E240868

UM-PRO PCB C-LOCK L1 BK - Locking



2200164

<https://www.phoenixcontact.com/us/products/2200164>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-PRO PCB C-LOCK L1 BK - Locking



2200164

<https://www.phoenixcontact.com/us/products/2200164>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.001 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com