ME-SAS MINI - Shield connection clamp

2200456

https://www.phoenixcontact.com/us/products/2200456

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection clamp for terminal points starting from 1.5 mm^2

Your advantages

- Safe discharge of interference signals
- Low transfer impedance due to large-surface shield connection
- Convenient mounting of the cable shielding

Commercial data

Item number	2200456
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHADZ
GTIN	4046356584333
Weight per piece (including packing)	6.21 g
Weight per piece (excluding packing)	6.21 g
Customs tariff number	73269098
Country of origin	DE

Technical data

Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME

Dimensions

Clamping range of the strain relief clip	ø 4.50 mm ... 8.00 mm

Material specifications

Color	silver-colored
Material Housing	Steel
Surface characteristics	galvanized

Mounting

Mounting type	Screw mounting

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.216 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com