

# ME B-17,5 MSTBO GYBN - Filler plug

2200558

<https://www.phoenixcontact.com/us/products/2200558>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points (MSTBO), width: 15 mm, height: 19.05 mm, depth: 12.3 mm, color: gray brown (similar RAL 8019)

Figure shows standard item in light gray

## Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

## Commercial data

Item number	2200558
Packing unit	10 pc
Minimum order quantity	500 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4055626305790
Weight per piece (including packing)	1.07 g
Weight per piece (excluding packing)	1.07 g
Country of origin	DE

# ME B-17,5 MSTBO GYBN - Filler plug



2200558

<https://www.phoenixcontact.com/us/products/2200558>

## Technical data

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Product family	ME 17,5..
Ventilation openings present	no

### Dimensions

Width	15 mm
Height	19.05 mm
Depth	12.3 mm

### Material specifications

Color (Filler plug)	gray brown (RAL 8019)
Material Filler plug	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

### Environmental and real-life conditions

#### Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

#### Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

#### Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

#### Mechanical strength / tumbling barrel

Specification	IEC 60998-1:2002-12
Height of fall	50 cm

# ME B-17,5 MSTBO GYBN - Filler plug



2200558

<https://www.phoenixcontact.com/us/products/2200558>

Frequency	10
-----------	----

## Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

## Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

## Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

## Mounting

Mounting type	Latching
---------------	----------

# ME B-17,5 MSTBO GYBN - Filler plug



2200558

<https://www.phoenixcontact.com/us/products/2200558>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200558>



**UL Recognized**

Approval ID: E240868

# ME B-17,5 MSTBO GYBN - Filler plug



2200558

<https://www.phoenixcontact.com/us/products/2200558>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME B-17,5 MSTBO GYBN - Filler plug



2200558

<https://www.phoenixcontact.com/us/products/2200558>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.02 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)