

EG MF 17,5 - Base latch

2200638

<https://www.phoenixcontact.com/us/products/2200638>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base latch, for DIN rail mounting, with spring included



Similar figure

Commercial data

Item number	2200638
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHCGZ
GTIN	4046356644402
Weight per piece (including packing)	3.539 g
Weight per piece (excluding packing)	3.539 g
Country of origin	DE

EG MF 17,5 - Base latch

2200638

<https://www.phoenixcontact.com/us/products/2200638>



Technical data

Product properties

Product type	Base latches
Housing type	Component housing
Housing series	EG
Product family	EG

Dimensions

Width	17.5 mm
Height	23.4 mm
Depth	6.5 mm

Material specifications

Material	Steel
----------	-------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EG MF 17,5 - Base latch

2200638

<https://www.phoenixcontact.com/us/products/2200638>



Classifications

ECLASS

ECLASS-15.0	27190605
ECLASS-13.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EG MF 17,5 - Base latch

2200638

<https://www.phoenixcontact.com/us/products/2200638>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.011 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com