

2200766

<https://www.phoenixcontact.com/us/products/2200766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Intermediate element, tall design, with vents, width: 22.6 mm, height: 99 mm, depth: 112.85 mm, color: blue gray (similar RAL 7031), cross connection: without bus connector

Your advantages

- Easy installation
- Variety of connection technology
- Can be mounted on the DIN rail

Commercial data

Item number	2200766
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4046356672146
Weight per piece (including packing)	27.14 g
Weight per piece (excluding packing)	19.53 g
Country of origin	DE

ME MAX 45 MT CL 3-3 BUGY - Intermediate element



2200766


<https://www.phoenixcontact.com/us/products/2200766>

Technical data

Product properties

Product type	Complete housing center part
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 45..
Number of positions	24
Number of rows	3
Number (Connection openings)	6
Ventilation openings present	yes
Anzahl der Etagen Housing (Makro)	3 (Both sides)

Dimensions

Dimensional drawing	
Width	22.6 mm
Height	99 mm
Depth	112.85 mm
Depth from top edge of DIN rail	107 mm

Material specifications

Color (Intermediate element)	blue gray (RAL 7031)
Material Intermediate element	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

PCB data

ME MAX 45 MT CL 3-3 BUGY - Intermediate element



2200766

<https://www.phoenixcontact.com/us/products/2200766>

Type of PCB mount	Latching
-------------------	----------

Mounting


Mounting type	Latching with housing half-shell or intermediate element
---------------	--

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

ME MAX 45 MT CL 3-3 BUGY - Intermediate element



2200766

<https://www.phoenixcontact.com/us/products/2200766>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200766>



UL Recognized

Approval ID: E240868

ME MAX 45 MT CL 3-3 BUGY - Intermediate element



2200766

<https://www.phoenixcontact.com/us/products/2200766>

Classifications

ECLASS

ECLASS-13.0	27190604
ECLASS-15.0	27190604

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 45 MT CL 3-3 BUGY - Intermediate element



2200766

<https://www.phoenixcontact.com/us/products/2200766>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.164 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com