

HC-ALU 6 MOUNT 150 GY - Mounting material



2200912

<https://www.phoenixcontact.com/us/products/2200912>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting foot for panel mounting the HC-ALU panel mounting base



Your advantages

- Aluminum extruded profile
- Available in lengths from 100 mm ... 1000 mm, can be cut to any length
- Available in overall widths from 53.5 mm ... 161 mm
- Up to IP65 degree of protection
- Can be used as handheld and wall housing
- Optional EMC seals available

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2200912 |
| Packing unit | 2 pc |
| Minimum order quantity | 2 pc |
| Sales key | AC02 |
| Product key | ACFAAZ |
| GTIN | 4046356716864 |
| Weight per piece (including packing) | 45.4 g |
| Weight per piece (excluding packing) | 43.4 g |
| Customs tariff number | 76169990 |
| Country of origin | HU |

HC-ALU 6 MOUNT 150 GY - Mounting material



2200912

<https://www.phoenixcontact.com/us/products/2200912>

Technical data

Product properties

| | |
|----------------|-------------------|
| Product type | Mounting material |
| Housing type | Profile housing |
| Housing series | HC-ALU |
| Product family | HC-ALU |

Dimensions

| | |
|--------|----------|
| Length | 154.4 mm |
|--------|----------|

HC-ALU 6 MOUNT 150 GY - Mounting material



2200912

<https://www.phoenixcontact.com/us/products/2200912>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HC-ALU 6 MOUNT 150 GY - Mounting material



2200912

<https://www.phoenixcontact.com/us/products/2200912>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com