

UM-ALU 4-72 FRONT 990 - Front plate



2200932

<https://www.phoenixcontact.com/us/products/2200932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Basic profile front plate, width: 71.8 mm, length: 991.3 mm, depth: 2 mm, recommended for UM-ALU 4-..COVER PA.. lateral elements



Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2200932 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | ACHDFC |
| GTIN | 4046356720878 |
| Weight per piece (including packing) | 386 g |
| Weight per piece (excluding packing) | 386 g |
| Country of origin | DE |

UM-ALU 4-72 FRONT 990 - Front plate



2200932

<https://www.phoenixcontact.com/us/products/2200932>

Technical data

Product properties

| | |
|------------------------------|------------------------------|
| Product type | Component housing cover |
| Housing type | Press-drawn section housings |
| Housing series | UM-ALU |
| Product family | UM-ALU 4-72 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|----------|
| Width | 71.8 mm |
| Depth | 2 mm |
| Length | 991.3 mm |

Material specifications

| | |
|-------------------------|---------------------|
| Color (Housing) | aluminum color |
| Material Housing | Aluminum (anodized) |
| Surface characteristics | anodized |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP40 |
| Ambient temperature (operation) | -40 °C ... 100 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |

UM-ALU 4-72 FRONT 990 - Front plate


2200932

<https://www.phoenixcontact.com/us/products/2200932>



Drawings

Schematic diagram



UM-ALU 4-72 FRONT 990 - Front plate



2200932

<https://www.phoenixcontact.com/us/products/2200932>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-ALU 4-72 FRONT 990 - Front plate



2200932

<https://www.phoenixcontact.com/us/products/2200932>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com