

ME MAX 12,5 PLATE KMGY - Insertion plate



2201256

<https://www.phoenixcontact.com/us/products/2201256>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 9.2 mm, height: 73.6 mm, depth: 1 mm, color: light gray (similar RAL 7035)



Figure shows one version

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2201256 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHABZ |
| GTIN | 4046356751025 |
| Weight per piece (including packing) | 0.98 g |
| Weight per piece (excluding packing) | 0.98 g |
| Country of origin | DE |

ME MAX 12,5 PLATE KMGY - Insertion plate



2201256

<https://www.phoenixcontact.com/us/products/2201256>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|------------------|
| Product type | Cover |
| Housing type | DIN rail housing |
| Housing series | ME-MAX |
| Product family | ME MAX 12,5.. |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 9.2 mm |
| Height | 73.6 mm |
| Depth | 1 mm |

Material specifications

| | |
|--|-----------------------|
| Color (Insertion plate) | light gray (RAL 7035) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |
| Surface characteristics | untreated |

ME MAX 12,5 PLATE KMGY - Insertion plate



2201256

<https://www.phoenixcontact.com/us/products/2201256>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME MAX 12,5 PLATE KMGY - Insertion plate



2201256

<https://www.phoenixcontact.com/us/products/2201256>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com