

UM-ALU 4-100,5 COVERLID 75 AL - Lateral element



2201760

<https://www.phoenixcontact.com/us/products/2201760>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Screw mounting, Side elements (left and right) incl. snap-on foot and screws for profile cover UM-ALU 4 AU..L..., width: 105.4 mm, height: 2 mm, depth: 73.5 mm



Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

Commercial data

Item number	2201760
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC14
Product key	ACHDFC
GTIN	4046356909068
Weight per piece (including packing)	74.2 g
Weight per piece (excluding packing)	72.8 g
Customs tariff number	76161000
Country of origin	DE

UM-ALU 4-100,5 COVERLID 75 AL - Lateral element



2201760

<https://www.phoenixcontact.com/us/products/2201760>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM-ALU
Product family	UM-ALU 4-100,5
Ventilation openings present	no

Dimensions

Width	105.4 mm
Height	2 mm
Depth	73.5 mm

Material specifications

Color (Side element)	aluminum color
Material Lateral element	Aluminum (anodized)
Surface characteristics	anodized

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

Mounting

Mounting type	Screw mounting
Tightening torque / speed	Screw connection with header/profile cover: 0.8 Nm-1 Nm / rpm-rpm

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-ALU 4-100,5 COVERLID 75 AL - Lateral element


2201760

<https://www.phoenixcontact.com/us/products/2201760>



Drawings

Schematic diagram



UM-ALU 4-100,5 COVERLID 75 AL - Lateral element



2201760

<https://www.phoenixcontact.com/us/products/2201760>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-ALU 4-100,5 COVERLID 75 AL - Lateral element



2201760

<https://www.phoenixcontact.com/us/products/2201760>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com