HSC-LR 9U KIT 2003 - Locking

2201794

https://www.phoenixcontact.com/us/products/2201794

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, 9U, Lock and Release system, width: 16.1 mm, height: 111.8 mm, depth: 8.8 mm, color: orange (similar RAL 2003)

Your advantages

- Easy, tool-free mounting
- Lock and Release interlock in contrasting color for intuitive operation
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2201794
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC15
Product key	ACHECZ
GTIN	4046356933599
Weight per piece (including packing)	5.8 g
Weight per piece (excluding packing)	4.1 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Notes

Assembly note	Please observe the application note in the download area.

Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME-IO
Product family	ME-IO

Dimensions

Width	16.1 mm
Height	111.8 mm
Depth	8.8 mm

Material specifications

Color	orange (RAL 2003)
Material	PA6-GF30
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2201794

UL Recognized
Approval ID: E240868

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.043 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com