

HS LC-V-D3/ R3XC1-5,08 - Fiber optic

2202312

<https://www.phoenixcontact.com/us/products/2202312>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiple light guides, passive, rigid, Cylinder head, emission surface: planar, number of displays: 3, (3 rows, 1 column), pitch: 5.08 mm, ESD protection: <12 kV, can be used for the BC housing range (housing must be processed)

Your advantages

- Light guides are perfectly matched to electronics housings
- Easy mounting on the PCB using press pins
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

Commercial data

Item number	2202312
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	AC05
Product key	ACGABB
GTIN	4055626049939
Weight per piece (including packing)	1.018 g
Weight per piece (excluding packing)	1.011 g
Customs tariff number	39269097
Country of origin	TN

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Fiber optic
Number of positions	3
Pitch	5.08 mm
Number of rows	3
Alignment	Vertical
Conductor type	Multiple light guides
Head form	Cylinder head
Number of indicators	3 (3 rows x 1 column)

Electrical properties

ESD protection	< 12 kV
----------------	---------

Dimensions

Diameter	3 mm
Hole diameter	2.4 mm
Pitch	5.08 mm

Material specifications

Color (Light guide)	transparent
Material Light guide	Polycarbonate
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Mounting

Mounting type	Press-in
---------------	----------

HS LC-V-D3/ R3XC1-5,08 - Fiber optic



2202312

<https://www.phoenixcontact.com/us/products/2202312>

Classifications

ECLASS

ECLASS-13.0	27460404
ECLASS-15.0	27460404

ETIM

ETIM 10.0	EC002943
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

2202312

<https://www.phoenixcontact.com/us/products/2202312>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.033 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com