

ME MAX 12,5 PLATE YE - Insertion plate



2202597

<https://www.phoenixcontact.com/us/products/2202597>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 9.2 mm, height: 73.6 mm, depth: 1 mm, color: yellow (similar RAL 1018)



The figure shows a similar product

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2202597
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4055626158884
Weight per piece (including packing)	1.01 g
Weight per piece (excluding packing)	0.8 g
Country of origin	DE

ME MAX 12,5 PLATE YE - Insertion plate



2202597

<https://www.phoenixcontact.com/us/products/2202597>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 12,5..
Ventilation openings present	no

Dimensions

Width	9.2 mm
Height	73.6 mm
Depth	1 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Material Housing	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

PCB data

Type of PCB mount	Latching
-------------------	----------

Mounting

Mounting type	Slot
---------------	------

ME MAX 12,5 PLATE YE - Insertion plate



2202597

<https://www.phoenixcontact.com/us/products/2202597>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 12,5 PLATE YE - Insertion plate



2202597

<https://www.phoenixcontact.com/us/products/2202597>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.019 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com