

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell

2202873

<https://www.phoenixcontact.com/us/products/2202873>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Housing half shell (right), tall design, without vents, width: 11.3 mm, height: 99 mm, depth: 112.85 mm, color: light gray (similar RAL 7035), cross connection: DIN rail bus connector (optional)

Your advantages

- Easy installation
- Variety of connection technology

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2202873 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | ACHABZ |
| GTIN | 4055626383248 |
| Weight per piece (including packing) | 24.528 g |
| Weight per piece (excluding packing) | 23.846 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell

2202873

<https://www.phoenixcontact.com/us/products/2202873>

Technical data


Notes

| | |
|----------------|---|
| Assembly note | Please observe the application note in the download area. |
| Recommendation | Material of contact pads for bus connector, galvanic gold (hard gold) |

Product properties

| | |
|-----------------------------------|---------------------|
| Product type | Housing half shells |
| Housing type | DIN rail housing |
| Housing series | ME-MAX |
| Product family | ME MAX.. G 2-2 |
| Number of rows | 2 |
| Number (Connection openings) | 4 |
| Ventilation openings present | no |
| Anzahl der Etagen Housing (Makro) | 2 (Both sides) |

Dimensions

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Width | 11.3 mm |
| Height | 99 mm |
| Depth | 112.85 mm |
| Depth from top edge of DIN rail | 107 mm |

PCB design

| | |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell



2202873

<https://www.phoenixcontact.com/us/products/2202873>

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

PCB data

| | |
|----------------------|-------------------|
| Type of PCB mount | Latching |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

Mounting

| | |
|---------------|--|
| Mounting type | Latching with housing half-shell or intermediate element |
|---------------|--|

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell

2202873

<https://www.phoenixcontact.com/us/products/2202873>

Drawings

Dimensional drawing



Schematic view

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell



2202873

<https://www.phoenixcontact.com/us/products/2202873>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME MAX 17,5 GEH-R CL G 2-2KMGY - Housing half shell



2202873

<https://www.phoenixcontact.com/us/products/2202873>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.142 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com