HCS-C MINI-P 1W C C C 7035 - Electronics housing

2203153

https://www.phoenixcontact.com/us/products/2203153

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

Commercial data

Item number	2203153
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFACA
GTIN	4055626377063
Weight per piece (including packing)	132.9 g
Weight per piece (excluding packing)	93 g
Customs tariff number	84879090
Country of origin	DE

Technical data


Product properties

Product type	Complete housing
Housing type	Handheld housing
Housing type	Handheld housing
Housing series	HCS
Ventilation openings present	no
Battery compartment	no

Display

Diagonal	2.8 in. / 7 cm (Window for display)

Dimensions

Dimensional drawing	
Width	80 mm
Height	135 mm
Depth	29 mm
Dimensions	70.4 mm x 69.2 mm x 1.1 mm (Recessed area on front)
	70.4 mm x 8.2 mm x 1.1 mm (Recessed area on front)
	63 mm x 34 mm (Window for display)
	70.4 mm x 43 mm x 2.5 mm (Holder for cover lens)

PCB design

PCB thickness	1.4 mm ... 1.8 mm

Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	ABS
Flammability rating according to UL 94	V0
CTI according to IEC 60112	400 ≤ CTI < 600

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02

Temperature	80 °C
Test duration	1 h
Force	20

Ambient conditions

Max. IP code to attain	IP54
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C
Relative humidity (storage/transport)	95 %

PCB data


Number of PCB holders	2
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Tightening torque / speed	Screw connection between housing halves: 0.25 - 0.3 Nm / 500 - 1000 rpm
Tightening torque	0.25 Nm ... 0.3 Nm

Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

Classifications

ECLASS

ECLASS-13.0	27190102
ECLASS-15.0	27190102

ETIM

ETIM 9.0	EC001031

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com