

HC-ALU 6-78 DKL-COVER2 GY - End cover



2203468

<https://www.phoenixcontact.com/us/products/2203468>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing, Screw mounting, End cover, with hinged flap, with screws and seal, for 53.5 mm profile width (internal), depth: 78 mm

The figure shows the standard item

Your advantages

- Aluminum extruded profile
- Available in lengths from 100 mm ... 1000 mm, can be cut to any length
- Available in overall widths from 53.5 mm ... 161 mm
- Up to IP65 degree of protection
- Can be used as handheld and wall housing
- Optional EMC seals available

Commercial data

Item number	2203468
Packing unit	1 pc
Minimum order quantity	5 pc
Product key	ACFAAC
GTIN	4055626385693
Weight per piece (including packing)	123 g
Weight per piece (excluding packing)	123 g
Country of origin	HU

HC-ALU 6-78 DKL-COVER2 GY - End cover



2203468

<https://www.phoenixcontact.com/us/products/2203468>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU 6-78
Ventilation openings present	no

Dimensions

Depth	78 mm
-------	-------

Material specifications

Color (Housing)	graphite gray (RAL 7024)
Surface characteristics	powder coated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP65
------------------------	------

Mounting

Mounting type	Screw mounting
---------------	----------------

HC-ALU 6-78 DKL-COVER2 GY - End cover



2203468

<https://www.phoenixcontact.com/us/products/2203468>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-ALU 6-78 DKL-COVER2 GY - End cover



2203468

<https://www.phoenixcontact.com/us/products/2203468>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com