
# HCS-T MINI WIN 1,0 FR128X64 - Washer/ring

2203590

https://www.phoenixcontact.com/us/products/2203590

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Acrylic glass, satin-finished, frame printed black, for display 128x64



## Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

## Commercial data

| | |
|---|---|
| Item number | 2203590 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC02 |
| Product key | ACFACZ |
| GTIN | 4055626485324 |
| Weight per piece (including packing) | 5.9 g |
| Weight per piece (excluding packing) | 5.9 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Mounting material |
| Housing type | Handheld housing |
| Housing series | HCS |

### Dimensions

| | |
|---|---|
| Width | 64.6 mm |
| Depth | 1.5 mm |
| Dimensions | 60.9 mm x 31.9 mm |

### Material specifications

| | |
|---|---|
| Color (Housing) | transparent |
| Material | PMMA |

### Environmental and real-life conditions

Glow-wire test

| | |
|---|---|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---|---|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 80 °C |
| Test duration | 1 h |
| Force | 20 |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

| | |
|---|---|
| ETIM 9.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com