

UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block



1953525

<https://www.phoenixcontact.com/us/products/1953525>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, 1 level, connection method: Spade connection, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting: NS 35/7,5, NS 35/15, NS 32, color: gray

Commercial data

Item number	1953525
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BE511X
GTIN	4017918240677
Weight per piece (including packing)	17.35 g
Weight per piece (excluding packing)	17.35 g
Country of origin	PL

UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block



1953525

<https://www.phoenixcontact.com/us/products/1953525>

Technical data

Product properties

Product type	Hybrid terminal block
Number of connections	8
Number of rows	2
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
---------------------	------

Connection data

Number of connections per level	8
Nominal cross section	4 mm ²

1 level

Connection method	Spade connection
TERMI-POINT pin dimensions	2.4 x 0.8 mm
Position of the TERMI-POINT pin	horizontal
Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Cross section AWG	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Nominal cross section	4 mm ²
Nominal current	32 A (dependent on the slip-on connection sleeve)
Maximum load current	32 A (dependent on the slip-on connection sleeve)
Nominal voltage	800 V (voltage data for slip-on connections in acc. with EN 61210 are also dependent on nominal size, material, insulation of the sleeve and conductor cross-section.)

Dimensions

Width	6.2 mm
End cover width	2.2 mm

Material specifications

Color	gray
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block



1953525

<https://www.phoenixcontact.com/us/products/1953525>

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block




1953525

<https://www.phoenixcontact.com/us/products/1953525>

Drawings

Circuit diagram




UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block

1953525

<https://www.phoenixcontact.com/us/products/1953525>

Circuit diagram



- 1 = cover
- 2 = fixed bridge
- 3 = insertion bridge
- 4 = isolator bridge bar
- 5 = bridge bar isolator
- 6 = separating plate
- 7 = partition plate
- 8 = test plug socket

UVKB 4-FS/FS(2,8)TP(2,4)1234/Q - Feed-through terminal block



1953525

<https://www.phoenixcontact.com/us/products/1953525>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com