


# SK 5,08/3,8 DN - Marker card

1965458

<https://www.phoenixcontact.com/us/products/1965458>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Card, white (RAL 9010), labeled, mounting type: adhesive, for terminal block width: 5.08 mm

## Commercial data

Item number	1965458
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG05
Product key	BG2123
GTIN	4017918927271
Weight per piece (including packing)	0.8 g
Weight per piece (excluding packing)	0.446 g
Customs tariff number	39199080
Country of origin	DE

# SK 5,08/3,8 DN - Marker card



1965458

<https://www.phoenixcontact.com/us/products/1965458>

## Technical data

### Product properties

Product type	Terminal marker
Number of positions	5
Pitch	5.08 mm

### Marking

Number of marker strips	12
Identification technology	Thermotransfer

### Dimensions

Width	25.00 mm
Height	3.80 mm
Depth	0.12 mm
Pitch	5.08 mm

### Material specifications

Foil strength	100 µm
Adhesive strength	15 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Base element material	Polyethylene
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

# SK 5,08/3,8 DN - Marker card



1965458

<https://www.phoenixcontact.com/us/products/1965458>

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Mounting

Mounting type	adhesive
---------------	----------

# SK 5,08/3,8 DN - Marker card



1965458

<https://www.phoenixcontact.com/us/products/1965458>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SK 5,08/3,8 DN - Marker card



1965458

<https://www.phoenixcontact.com/us/products/1965458>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)