

SFL (2,8-0,8)D32 - Female connector strip


2285302

<https://www.phoenixcontact.com/us/products/2285302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



BOX



19" socket strip, color: green, number of positions: 32, product range: SFL (2,8-0,8), pitch: 0 mm, type of packaging: packed in cardboard

Your advantages

- Space-saving, standardized slip-on connection allows worldwide use
- Conductor connection on several levels enables higher contact density

Commercial data

Item number	2285302
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AA08
Product key	AAHHCA
GTIN	4017918055905
Weight per piece (including packing)	30.05 g
Weight per piece (excluding packing)	28.71 g
Customs tariff number	85369010
Country of origin	PL

SFL (2,8-0,8)D32 - Female connector strip

2285302

<https://www.phoenixcontact.com/us/products/2285302>

Technical data

Notes

Notes on operation	In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load.
--------------------	--

Product properties

Product type	19" socket strip
Product family	SFL (2,8-0,8)
Product line	COMBICON Connectors Special
Type	D
Number of positions	32
Pitch	0 mm
Number of rows	2

Electrical properties


Properties

Rated surge voltage (III/3)	2.5 kV
-----------------------------	--------

Connection data

Connection method	Spade connection
-------------------	------------------

Dimensions

Dimensional drawing	
Pitch	0 mm
Width [w]	95 mm
Height [h]	27.6 mm
Length [l]	10.6 mm

PCB design

Hole diameter	2.8 mm
---------------	--------

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
------	--

SFL (2,8-0,8)D32 - Female connector strip



2285302

<https://www.phoenixcontact.com/us/products/2285302>

Contact material	Cu alloy
Metal surface terminal point (top layer)	Gold (0.8 µm - 1.4 µm Au)
Metal surface terminal point (middle layer)	Nickel (2 µm - 4 µm Ni)
Metal surface contact area (top layer)	Gold (0.8 µm - 1.4 µm Au)
Metal surface contact area (middle layer)	Nickel (2 µm - 4 µm Ni)

Material data - housing

Color (Housing)	green (6021)
Insulating material group	II

Electrical tests

Air clearances and creepage distances |

Insulating material group	II
Rated surge voltage (III/3)	2.5 kV

Environmental and real-life conditions

Ambient conditions

Relative humidity (storage/transport)	30 % ... 70 %
---------------------------------------	---------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------


SFL (2,8-0,8)D32 - Female connector strip

2285302

<https://www.phoenixcontact.com/us/products/2285302>



Drawings



SFL (2,8-0,8)D32 - Female connector strip



2285302

<https://www.phoenixcontact.com/us/products/2285302>

Classifications

ECLASS

ECLASS-13.0	27460101
ECLASS-15.0	27460101

ETIM

ETIM 10.0	EC002643
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SFL (2,8-0,8)D32 - Female connector strip



2285302

<https://www.phoenixcontact.com/us/products/2285302>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.292 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com