

FLKM 50-PA-S135/P - Front adapter



2288587

<https://www.phoenixcontact.com/us/products/2288587>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Siemens SIMATIC® S5-135U, 1x 32 channels can be connected

The figure shows versions FLKM 50-PA-S135/P and FLKM 50/4-FLK14/PA-S135

Commercial data

Item number	2288587
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK231S
GTIN	4017918057107
Weight per piece (including packing)	189.92 g
Weight per piece (excluding packing)	189.92 g
Customs tariff number	85369010
Country of origin	DE

FLKM 50-PA-S135/P - Front adapter



2288587

<https://www.phoenixcontact.com/us/products/2288587>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 25 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 0.5 A
Current (per connection)	≤ 8 A (Feed-in via separate power supply)
Current (Total current per byte)	≤ 2 A (Feed-in via connector)

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

Connection data

Field level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Assembly note	in rows with zero spacing
---------------	---------------------------

FLKM 50-PA-S135/P - Front adapter



2288587

<https://www.phoenixcontact.com/us/products/2288587>

Mounting position	any
-------------------	-----

Notes

Notes on operation	No additional touch protection is required when using a SELV/PELV voltage (≤ 25 V AC or 60 V DC).
Notes on operation	At least one functional insulation against adjacent modules is complied with (in the support rail direction). If the application has stricter requirements for the insulation (basic insulation or reinforced insulation), they must be realized by applying suitable measures (e. g. partition plates).
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

FLKM 50-PA-S135/P - Front adapter




2288587

<https://www.phoenixcontact.com/us/products/2288587>

Drawings

Circuit diagram



FLKM 50-PA-S135/P - Front adapter



2288587

<https://www.phoenixcontact.com/us/products/2288587>

Classifications

ECLASS

ECLASS-13.0	27242292
-------------	----------

UNSPSC

UNSPSC 21.0	32151601
-------------	----------

FLKM 50-PA-S135/P - Front adapter



2288587

<https://www.phoenixcontact.com/us/products/2288587>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com