

FLKMS-D15 SUB/S/ZFKKDS/PE - Termination board



2295978

<https://www.phoenixcontact.com/us/products/2295978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with spring-cage connection and one D-SUB miniature pin strip, integrated PE contact for connecting the PCB and DIN rail, 15-pos.

Commercial data

Item number	2295978
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2A82
GTIN	4017918448011
Weight per piece (including packing)	123.7 g
Weight per piece (excluding packing)	89.57 g
Customs tariff number	85369010
Country of origin	DE

2295978

<https://www.phoenixcontact.com/us/products/2295978>

Technical data

Product properties

Product type	Interface module
Number of positions	15

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	25 V AC (60 V DC)
Max. current carrying capacity per branch	2.5 A

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 μ s)

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Spring-cage connection
Number of positions	16
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 14

Controller level

Connection method	D-SUB pin strip
Number of positions	15

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	64 mm
Height	90 mm
Depth	62 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

FLKMS-D15 SUB/S/ZFKKDS/PE - Termination board



2295978

<https://www.phoenixcontact.com/us/products/2295978>

Housing insulation material	PVC
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKMS-D15 SUB/S/ZFKKDS/PE - Termination board



2295978

<https://www.phoenixcontact.com/us/products/2295978>

Classifications

ECLASS

ECLASS-13.0

27141152

ETIM

ETIM 9.0

EC002780

UNSPSC

UNSPSC 21.0

39121400

2295978

<https://www.phoenixcontact.com/us/products/2295978>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com