

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, 1st level connection left, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.2 mm² - 4 mm², connection method: Spade connection, mounting: NS 32, color: gray

Your advantages

- User-friendly operation, i.e., unobstructed view of plugs, good access to plugs, and fast connection check
- Designation read from the front
- Attractive appearance due to the elegant conductor conduit in the lateral cable ducts
- Terminal blocks and bridge connections eliminated

Commercial data

Item number	2017017
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE05
Product key	BE511X
GTIN	4017918052652
Weight per piece (including packing)	11.15 g
Weight per piece (excluding packing)	10.99 g
Customs tariff number	85369010
Country of origin	PL

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Technical data

Product properties

Product type	Hybrid terminal block
Number of connections	9
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	9
Nominal cross section	4 mm ²

1st level connection left

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	9 mm
Internal cylindrical gage	A3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, rigid	4 mm ²
Cross-section with insertion bridge, flexible	4 mm ²
2 conductors with same cross section, rigid	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 2.5 mm ²
Nominal cross section	4 mm ²
Nominal current	32 A
Maximum load current	40 A (with 4 mm ² conductor cross-section)
Nominal voltage	800 V
Connection method	Spade connection

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Dimensions

Width	6.2 mm
End cover width	2.3 mm
Height	54 mm
Depth on NS 32	56.5 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 32
---------------	-------

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Drawings

Circuit diagram




HK 4-FS(8-2,8-0,8) - Feed-through terminal block

2017017

<https://www.phoenixcontact.com/us/products/2017017>

Circuit diagram



- 1 = cover
- 2 = fixed bridge
- 3 = insertion bridge
- 4 = isolator bridge bar
- 5 = bridge bar isolator
- 6 = separating plate
- 7 = partition plate
- 8 = test plug socket

HK 4-FS(8-2,8-0,8) - Feed-through terminal block





2017017


<https://www.phoenixcontact.com/us/products/2017017>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2017017>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	20 A	28 - 14	-

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	250 V	25 A	28 - 12	-
C				
	150 V	25 A	28 - 12	-

 EAC Approval ID: RU C-DE.BL08.B.00541				
---	--	--	--	--

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Classifications

ECLASS

ECLASS-13.0	27250201
ECLASS-15.0	27250201

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HK 4-FS(8-2,8-0,8) - Feed-through terminal block



2017017

<https://www.phoenixcontact.com/us/products/2017017>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.089 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com