

EMG 75-REL/MR-G220/4X21/SO110 - Relay module



2301684

<https://www.phoenixcontact.com/us/products/2301684>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, contact (AgNi): medium to large loads, 4 changeover contacts, input voltage 220 V DC

Commercial data

Item number	2301684
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	DK614Y
GTIN	4017918960742
Weight per piece (including packing)	200 g
Weight per piece (excluding packing)	200 g
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Mechanical service life	3x 10 ⁷ cycles

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Test voltage (Winding/contact)	2 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (Contact/contact)	2 kV AC (50 Hz, 1 min., contact/contact)

Input data

Coil side

Nominal input voltage U_N	220 V DC
Input voltage range	176 V DC ... 242 V DC
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	4 mA
Typical response time	9 ms
Typical release time	10 ms
Protective circuit	Free-wheeling diode, polarity protection diode, resistor

Output data

Switching

Contact material	AgNi
Note	4 changeover contacts
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Interrupting rating (ohmic load) max.	140 W (at 24 V DC)
	85 W (at 48 V DC)
	60 W (at 60 V DC)
	44 W (at 110 V DC)

EMG 75-REL/MR-G220/4X21/SO110 - Relay module



2301684

<https://www.phoenixcontact.com/us/products/2301684>

	60 W (at 220 V DC)
	1500 VA (for 250 V AC)

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²

Contact side

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²

Dimensions

Width	75 mm
Height	75 mm
Depth	55 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	IEC 60664
	DIN VDE 0109-11, draft
	DIN VDE 0110
	IEC 60664A

Mounting

Mounting type	DIN rail mounting
Mounting position	any

2301684

<https://www.phoenixcontact.com/us/products/2301684>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com