

# UM-PRO 108 COVER-L BK S471 - Lateral element



2200764

<https://www.phoenixcontact.com/us/products/2200764>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting/panel mounting (with optional mounting flange), latching with extruded profile, Lateral element (left), width: 19.5 mm, height: 127.8 mm, depth: 39.45 mm



Product photo shows a standard item

## Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

## Commercial data

Item number	2200764
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC22
Product key	ACHDAA
GTIN	4055626122779
Weight per piece (including packing)	17.89 g
Weight per piece (excluding packing)	17.5 g
Customs tariff number	39269097
Country of origin	PL

2200764

<https://www.phoenixcontact.com/us/products/2200764>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM-PRO
Product family	UM-PRO 108

### Dimensions

Width	19.5 mm
Height	127.8 mm
Depth	39.45 mm
Depth from top edge of DIN rail	32.45 mm

### PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

### Material specifications

Color (Side element)	black (RAL 9005)
Material Lateral element	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

#### Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

#### Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

#### Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

# UM-PRO 108 COVER-L BK S471 - Lateral element



2200764

<https://www.phoenixcontact.com/us/products/2200764>

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

## PCB data

Number of PCB holders	3
Type of PCB mount	Insertion/securing with additional elements
Thickness of the PCB	1.4 mm ... 1.8 mm

## Mounting

Mounting type	DIN rail mounting/panel mounting (with optional mounting flange), latching with extruded profile
---------------	--

## Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM-PRO 108 COVER-L BK S471 - Lateral element



2200764

<https://www.phoenixcontact.com/us/products/2200764>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200764>



**UL Recognized**

Approval ID: E240868

# UM-PRO 108 COVER-L BK S471 - Lateral element



2200764

<https://www.phoenixcontact.com/us/products/2200764>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# UM-PRO 108 COVER-L BK S471 - Lateral element



2200764

<https://www.phoenixcontact.com/us/products/2200764>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.32 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)