# EH 45 F-C SS/ABS GY7035 - Upper housing part

2200789

https://www.phoenixcontact.com/us/products/2200789

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Upper housing part, flat design, connection opening on one side, connection opening on one side, width: 45.1 mm, height: 74.65 mm, depth: 36.95 mm, color: light gray (similar RAL 7035)

## Your advantages

- DIN rail or panel mounting for application-specific device attachment
- Easy design-in, thanks to variable housing form factor
- Complete flexibility, thanks to PCBs with horizontal, frontal, and orthogonal orientation to the front of the device
- Three cover versions for individual PCB connections
- Integration of a wide variety of PCB connection technologies for a functional device design

## Commercial data

| | |
|---|---|
| Item number | 2200789 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC12 |
| Product key | ACHCHC |
| GTIN | 4046356911177 |
| Weight per piece (including packing) | 20.2 g |
| Weight per piece (excluding packing) | 20.2 g |
| Customs tariff number | 84879090 |
| Country of origin | IN |

## Technical data


### Notes

| | |
|---|---|
| Assembly note | Please observe the application note in the download area. |

### Product properties

| | |
|---|---|
| Product type | Upper housing part |
| Housing type | DIN rail housing |
| Housing type | Basic housing |
| Housing series | EH |
| Product family | EH..F..ABS.. |
| Number (Connection openings) | 1 |
| Ventilation openings present | yes |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 45.1 mm |
| Height | 74.65 mm |
| Depth | 36.95 mm |
| Depth from base support surface | 19.95 mm |

### Material specifications

| | |
|---|---|
| Color (Upper housing part) | light gray (RAL 7035) |
| Material Upper housing part | ABS |
| Flammability rating according to UL 94 | HB |

### Environmental and real-life conditions

Vibration test

| | |
|---|---|
| Specification | IEC 60068-2-6:2007-12 |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration | 2g (58.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h |
| Test directions | X-, Y- and Z-axis |

Glow-wire test

| | |
|---|---|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---|---|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 80 °C |
| Test duration | 1 h |
| Force | 20 N |

Mechanical strength / tumbling barrel

| | |
|---|---|
| Specification | IEC 60998-1:2002-12 |
| Height of fall | 50 cm |
| Frequency | 10 |

Shocks

| | |
|---|---|
| Specification | IEC 60068-2-27:2008-02 |
| Pulse shape | Half-sine |
| Acceleration | 15g |
| Shock duration | 11 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

Degree of protection (IP code)

| | |
|---|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |

Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 80 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 80 °C |
| Relative humidity (storage/transport) | 95 % |

## PCB data

| | |
|---|---|
| Type of PCB mount | Slot |

## Mounting


| | |
|---|---|
| Mounting type | Snap in |

## Packaging specifications

| | |
|---|---|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |

## Drawings

Dimensional drawing




Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the “Downloads” tab.

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

### ETIM

| | |
|---|---|
| ETIM 9.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com