

ME MAX F-GL G 3-3 KMGY - Housing half shell

2201167

<https://www.phoenixcontact.com/us/products/2201167>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Housing half shell (left), flat design, without vents, width: 6.3 mm, height: 85 mm, depth: 90.35 mm, color: light gray (similar RAL 7035)

Figure shows complete housing

Your advantages

- Easy installation
- Variety of connection technology

Commercial data

Item number	2201167
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC22
Product key	ACHABA
GTIN	4046356736053
Weight per piece (including packing)	14.75 g
Weight per piece (excluding packing)	14.75 g
Customs tariff number	85389099
Country of origin	DE

ME MAX F-GL G 3-3 KMGY - Housing half shell

2201167


<https://www.phoenixcontact.com/us/products/2201167>

Technical data

Product properties

Product type	Housing half shells
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX.. F G 3-3
Number of rows	3
Number (Connection openings)	6
Ventilation openings present	no
Anzahl der Etagen Housing (Makro)	3 (Both sides)

Dimensions

Dimensional drawing	
Width	6.3 mm
Height	85 mm
Depth	90.35 mm
Depth from top edge of DIN rail	84.5 mm

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing half-shell)	light gray (RAL 7035)
Material Housing half-shell	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

ME MAX F-GL G 3-3 KMGY - Housing half shell



2201167

<https://www.phoenixcontact.com/us/products/2201167>

PCB data

Type of PCB mount	Latching
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Mounting type	Latching with housing half-shell or intermediate element
---------------	--

ME MAX F-GL G 3-3 KMGY - Housing half shell

2201167

<https://www.phoenixcontact.com/us/products/2201167>

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

ME MAX F-GL G 3-3 KMGY - Housing half shell



2201167

<https://www.phoenixcontact.com/us/products/2201167>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201167>



UL Recognized

Approval ID: E240868

ME MAX F-GL G 3-3 KMGY - Housing half shell



2201167

<https://www.phoenixcontact.com/us/products/2201167>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX F-GL G 3-3 KMGY - Housing half shell



2201167

<https://www.phoenixcontact.com/us/products/2201167>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.086 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com