

# UM 108-PROFIL L6,8CM GN - Profile



2201181

<https://www.phoenixcontact.com/us/products/2201181>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Basic profile, width: 400 mm, depth: 122.6 mm



The figure shows the UM 45-Profil CM version

## Commercial data

Item number	2201181
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	ACHDBA
GTIN	4046356742498
Weight per piece (including packing)	40.946 g
Weight per piece (excluding packing)	40.946 g
Country of origin	DE

# UM 108-PROFIL L6,8CM GN - Profile



2201181

<https://www.phoenixcontact.com/us/products/2201181>

## Technical data

### Product properties

Product type	Lower housing part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

### Dimensions

Width	400 mm
Depth	122.6 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Housing material	PVC
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-15 °C ... 50 °C

# UM 108-PROFIL L6,8CM GN - Profile



2201181

<https://www.phoenixcontact.com/us/products/2201181>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)