
ME-IO 18,8 FOOT CATCH KIT - Base latch

2201812

https://www.phoenixcontact.com/us/products/2201812

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base latch, for DIN rail mounting, with spring included



Your advantages

- Enables easy DIN rail mounting of housing modules

Commercial data

Item number	2201812
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AC15
Product key	ACHEBZ
GTIN	4046356912600
Weight per piece (including packing)	4.51 g
Weight per piece (excluding packing)	4.51 g
Customs tariff number	73269098
Country of origin	CN

Technical data

Product properties

Product type	Base latches
Housing type	DIN rail housing
Housing type	Multifunctional housings
Housing series	ME-IO
Product family	ME-IO 18,8

Dimensions

Width	17.5 mm
Height	35.47 mm
Depth	6.5 mm

Material specifications

Color	silver-colored
Material	Steel (tin-plated)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.033 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com